


## 有機酸の分離

## Organic acids

Sunniest RP-AQUA 5 $\mu$ m150 x 4.6 mm i.d.



Column: Sunniest RP-AQUA 5  $\mu$ m, 150 x 4.6 mm i.d.

Mobile phase:

A) 50 mM Ammonium phosphate + Phosphoric acid (pH 2.4)

B) 0.01% Trifluoroacetic acid (pH 2.9)

Flow rate: 1.0 mL/min

Temperature: 40 °C

Detection: UV@210 nm