


# MRX.

## Adjustable handles



ELESA Original design



Elesa Standards		Main dimensions										Mounting hole		Teeth no.	Weight
Code	Description	R	L	D	H	H <sub>1</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	d <sub>1</sub>	d <sub>6H</sub>	h	z	g	
141131	MRX.40 B-M5	42	50	18	32	35.5	29	6	14	12	M5	10	18	10	
141141	MRX.40 B-M6	42	50	18	32	35.5	29	6	14	12	M6	10	18	12	
141411	MRX.63 B-M6	63	73	23	43	46.5	37	8	17	15	M6	16	20	21	
141421	MRX.63 B-M8	63	73	23	43	46.5	37	8	17	15	M8	13	20	22	
142111	MRX.80 B-M8	80	92	28	54	58.5	47	10	22	19	M8	20	24	41	
142121	MRX.80 B-M10	80	92	28	54	58.5	47	10	22	19	M10	18	24	42	
142131	MRX.80 B-M12	80	92	28	54	58.5	47	10	22	19	M12	17	24	45	
142501	MRX.100 B-M10	100	114	33	65	69.5	54	12	25	25	M10	20	28	70	
142511	MRX.100 B-M12	100	114	33	65	69.5	54	12	25	25	M12	20	28	74	
142521	MRX.100 B-M14	100	114	33	65	69.5	54	12	25	25	M14	20	28	84	
142531	MRX.100 B-M16	100	114	33	65	69.5	54	12	25	25	M16	22	28	81	

### Lever body

Glass-fibre reinforced polyamide based (PA) technopolymer. Resistant to solvents, oils, greases and other chemical agents.

### Colour

Black, matte finish.

### Push button

Technopolymer, black colour, matte finish.

### Standard execution

Glass-fibre reinforced technopolymer clamping element with retaining pin, black colour, with knurling on the protruding part to make initial tightening easier. AISI 302 stainless steel return spring.  
Brass boss, threaded blind hole.

### Special executions on request

Lever body in RAL 2004 orange, RAL 7031 grey.

### Features and applications

Particularly suitable when the lever turning angle is limited owing to lack of space.

Compared to other types of adjustable handles with metal retaining screw this solution offers:

- absolute electric insulation for the operator
- no visible steel parts subject to rust
- more comfortable lever release.

### Stress resistance


Adjustable handles are generally used for repetitive clamping operations sometimes with very high-frequency.

Therefore, the stress resistance (i.e. the resistance to repeated tightening cycles) of the handle unit is particularly important and, especially, the strength of the toothed element which transmits the tightening force from the handle to the threaded element (boss or stud).

In fact, the results of several laboratory tests, performed with a special instrument that simulates the most severe use conditions, have shown that e.g. MRX.80 adjustable handle can withstand without yielding more than 100,000 tightening cycles, under the action of a force of 490 N (see graphic).

The special glass-fibre reinforced technopolymer enables the ELESA adjustable handles to guarantee stress resistance values which are much higher than the ones generated under normal working conditions.

NUMBER OF TIGHTENINGS



### Instructions of use

For clamping, lift the lever to disengage the clamping device teeth and bring it back to start position. By releasing the lever, the return spring automatically engages the teeth.



STANDARD MACHINE ELEMENTS WORLDWIDE

ELESA models all rights reserved in accordance with the law. Always mention the source when reproducing our drawings.