

L 50 cabinets can be used with:

Any McIntosh glass panel Panloc product with front panel dimensions 3-1/2 x 16. (MC 502)

L 52 cabinets can be used with:

A. Any glass panel Panloc product with front panel dimensions 5-5/16 x 16. (MA 6200, C 32, MC 2125, MR 78, etc.)

B. Any metal panel product with front panel dimensions 5-7/32 x 16. (MC 2120)

L 54 cabinets can be used with:

A. Any glass panel Panloc product with front panel dimensions 7 x 16-3/16. (MC 2105, MC 2205)

B. Any metal panel product with front panel dimensions 6-31/32 x 16. (MC 2200)

Mounting Instructions For L 50, L 52, and L54:

A. For Panloc products

1. Mount the Panloc brackets to the metal strips on the cabinet with the 6-32 x 3/8 machine screws from the cabinet hardware package. An extra thread-cutting screw has been provided in case a mounting hole needs to be rethreaded.
2. Remove the plastic feet from the equipment bottom cover and slide the unit in the cabinet engaging the aluminum rails on the bottom cover with the Panloc brackets.
3. When the unit stops at the adjust position, depress the 11/16" wide latches on either side of the unit and slide the unit fully in the cabinet. Depress the Panloc buttons on the front panel to lock the unit in place.

B. For Metal Panel Products

1. Remove the plastic feet from the equipment bottom cover and slide the unit in the cabinet.
2. Tip the cabinet up so the unit front panel is facing the ceiling.
3. Secure the unit through the two holes in the cabinet bottom with two #10 x 1-1/4 wood screws from the cabinet hardware package. (Do not over-tighten so as to distort the bottom cover of the unit, or use any screws longer than those supplied in the cabinet hardware package.)