





Standard orbital head for tube-to tube sheet TIG orbital welding



Head for aircooler geometry that allows passage over the water tank



Evolution of the standard orbital head with **AVC** system for arc height management







Digital inverter generator with integrated microprocessor

General features of the Giotto orbital heads



Exclusive TIG welding torch

Unique product of its kind. The new orbital TIG torch has been designed and manufactured entirely by Maus Italia.



Filler wire driving system

The constant flow and rotation of the spool on the orbital axis increases the accuracy and quality of the weld.



Single key settings

Exclusive capability to adjust the geometry of the weld with the single supplied key.



Constant angular velocity

The adjustment system, with its 2-channel, 256-pulse digital encoder with continuous feedback, ensures a uniform and accurate weld.



In-house design and manufacture





Orbital welding heads for tube-to-tube sheet TIG welding for the manufacture of tube bundle heat exchangers.

Maus Italia presents its new range of Giotto series orbital heads for tube to tubesheet TIG welding.

Following thousands hours of R&D, tests and prototyping, the result is an outstanding and unprecedented orbital welding head that is a masterpiece developed, manufactured and machined in Italy, with the extreme precision and quality you would expect from Maus Italia.

The series offers a range models for orbital heads which come with a generator of the latest technology and dedicated software.



Electrode angle of incidence

The system which we offer for each weld geometry is accurate and repeatable and facilitates geometric set-up operations.



Management of the welding arc

Continuous monitoring of the arc current ensures constant penetration throughout the weld.



STANDARD

For tubes from 10.0 to 51.0 mm (from 0.394" to 2.008")



BlockOut


Anti-dazzle protection.

Allows multiple operators to work simultaneously on the same tube sheet without the need for personal protective equipment (PPE).



24/7 use

Water cooling system inside the head for significant weld improvement and guaranteed repeatability.



RMicrometric adjustment


Device for adjusting the distance of the electrode from the tubesheet.


Complete range of tube centring devices consisting of HS cartridge holding spindles and HC self-centring cartridges.

GT-12


WTC thrust collar systems customised to the geometry of the tube and to the material to be welded with Maus Italia BlockOut screen for anti-dazzle protection.

Gas2 direct outlet especially for the use of the WTC-TT thrust collar when welding titanium tubes.





There is no need for service wrenches and replacement of the worn electrode is fast (you no longer need to dismantle the ceramic nozzle, its gas diffuser or the filler wire guide).



Wire feed unit

Fully adjustable in all directions. All manoeuvres can be performed with the single supplied key.








Standard orbital welding head for tube-to-tube sheet TIG welding.

Transparent protection

The movement and consumption of the filler wire is always under the operator's eye thanks to the transparent protective inspection window.



The **Giotto** orbital head is an unprecedented coalescing of new ideas.

The standard version has all the cutting-edge technological features designed by the Maus Italia R&D staff.

Only intensive use over time in our customers' modern workshops can show the high level of efficiency and quality of the welded product obtained with this new head which has been entirely created by Maus Italia.



Electrode angle of incidence

Thanks to the system's components which have preset angles, each welding geometry is accurate and repeatable.

Facilitates geometric setup operations as well as being extremely stable and robust.

**


Internal torch cooling system


This efficient system for cooling the Giotto orbital welding heads ensures:

- control over the internal temperature of the rotating joint even at high welding amps;
- continuous use in 24/7 shifts
- high quality of the weld pool (lower average temperature of the electrode and the protection gas crossing it)
- significant improvement in weld performance

Protruding tube geometry

Flush tube geometry

















It is now possible for multiple operators to work simultaneously on the same tube sheet without the need for personal protective equipment (PPE) which is often uncomfortable and slows down productivity.

Terms, definitions and symbols in TIG orbital welding

a bevel thickness (between the root and weld surface)

de external tube diameter


Clearance (between the external tube diameter and the tube sheet)

tube thickness

t1 cladding thickness

tube sheet thickness

X weld overflow



Protruding tube Flush tube Recessed tube










Orbital head for TIG tube-to-tube sheet welding with **AVC** control for continuous arc voltage monitoring.

Test X-ray

Tube 3/4" 14 BWG
Material 316L
Tube protrusion 5 mm (0.197")
Tube sheet thickness 125 mm (4.92")




Test X-ray

Tube 1" 18 BWG

Material 304L

Flush tube

Tube sheet thickness 72 mm (2.83")




In addition to all of the features that are supplied with the standard *Giotto* head, the *AVC* model includes automatic arc height control thanks to an innovative manoeuvring system for the torch electrode holder.

The system's main feature is control of the 2-dimensional distance of the electrode which, when suitably combined with the incidence angle of the torch, allows you to manage the height of the arc in both axial and radial directions from the tube being welded.

Automation is managed by a DC motor driven by an absolute encoder.





Mockup section detail

Maus Italia constantly performs tests on mockups which are analysed by specialist laboratories so that the welds performed by **Giotto** heads are always perfect.

Ohm's First Law relating to management of the voltaic arc in TIG orbital welding.


(Arc Voltage Control) is the automatic management of arc height during welding. The principle upon which is based is Ohm's Law: $R = \frac{V}{I}$


When equal to current intensity **I**, the distance of the electrode from the weld pool **R** is proportional to the voltage of the welding arc **V**. Continuous monitoring of the arc voltage **V** allows modulation of the distance R of the electrode from the weld pool with the aim of obtaining constant penetration across all of the weld.



















General features			
Duty Cycle	A (65%)	200	
Weld speed (max.)	rpm	6	
D standard tube	mm inches	25,4 1	
Welding head cooling		closed liquid circuit	
Weld geometry			
Flush tube		standard	
Tungsten			
• 2.4		standard	
Electrode distance adjust	ment mm inches	manual 12 0.472	
Wire	Î		
Wire speed		rotating on head	
Wire reel (weight/Ø)	kg/mm /bs/inches	1/100 2.21/3.93	
Recommended wire Ø	mm inches	0,8 0.0315	
Wire speed (max.)	cm/min inches/min	200 78	
Dimensions			
Dimensions (LxBxH)	mm inches	510+Lx150x400 20+Lx6x1	
Weight excluding cables and	d spool kg lbs	≈ 12 ≈ 26.45	
Cable length	m ft	6 19.7	
air cooler			
Plug diameter (min.)	mm inches	26,2 1.031	
Depth (max.)	mm inches	490 19.291	



Orbital head for typical aircooler geometry which allows passage over the water tank.

Maus Italia has garnered customer approval thanks to another personalised and innovative solution:

The special transformation which can be made with the extension to the *Giotto* standard torch allows you to reach the far end of the tube over the heat exchanger's water tank.

By passing through its locking cap, it is now possible to weld tubes in aircoolers, guaranteeing unprecedented seal quality.

The special attention paid to the design of the filler wire feed system, which rotates indefinitely with the electrode holder, allows you to reach extreme depths whilst maintaining a constant flow of material throughout the weld cycle.









HS and **HC**

HS Cartridge holder spindles and HC self-centring cartridges for Giotto series orbital heads for tube-to-tube sheet TIG welding.

Tube @		HC	HS Spindle
		Cartridge	
mm	Inches	Cod.	Cod.
10,0 ÷ 10,5	0.394 ÷ 0.413	HC-1	
10,5 ÷ 11,0	0.413 ÷ 0.433	HC-2	
11,0 ÷ 11,5	0.433 ÷ 0.453	HC-3	HS-A
11,5 ÷ 12,0	0.453 ÷ 0.472	HC-4	
12,0 ÷ 12,5	0.472 ÷ 0.492	HC-5	
12,5 ÷ 13,0	0.492 ÷ 0.512	HC-6	
12,8 ÷ 14,0	0.504 ÷ 0.551	HC-7	
100 150	0.540 . 0.500	1100	

HC-8

HC-9

HC-10

HC-11

HC-12

HS-B

 $0.543 \div 0.590$

 $0.583 \div 0.630$

 $0.622 \div 0.669$

 0.661 ± 0.709

 $0.701 \div 0.748$

 $13,8 \div 15,0$


 $14,8 \div 16,0$


 $15,8 \div 17,0$


 $16,8 \div 18,0$


 $17.8 \div 19.0$


Centring of the torch is guaranteed by the spindle + cartridge system. Select the correct combination of **HS** series spindle and **HC** series cartridge by referring to the table (left) according to the internal diameter of the tube.











These and other combinations only on request. Maus Italia technical staff are available for advice on the ideal solution.

Tubweld








In-house design and manufacturing

Each component of the **Giotto**TIG orbital heads has been
designed and manufactured
entirely by Maus Italia.



General features			
Duty Cycle	A (65%)	250	250
Weld speed (max.)	rpm	6	6
ID Tube	mm inches	10 <i>0.3</i> 93	10 0.393
OD standard tube	mm inches	51 2.008	51 2.008
Welding head cooling		closed liquid circuit	closed liquid circuit
Weld geometry			
Flush tube		standard	standard
Recessed tube	mm inches	3,0 0.118	NA
Protruding tube (max.)	mm inches	12,0 0.472	10,0 0.393
Tungsten			
• 1.6		opzional	opzional
• 2.4		standard	standard
• 3.2		opzional	opzional
Electrode distance adjustment	mm inches	manual 12 0.472	automatic AVC 12 0.472
Wire			
Wire speed		rotating on head	rotating on head
Wire reel (weight/Ø)	kg/mm lbs/inches	1/100 2.21/3.937	1/100 2.21/3.937
Recommended wire Ø	mm inches	0,8 0.0315	0,8 0.0315
Wire speed (max.)	cm/min inches/min	200 78	200 78
Dimensions			
Dimensions (LxBxH)	mm inches	510x150x400 20x6x16	510x150x400 20x6x16
Weight excluding cables and spool	kg lbs	12 26.45	13 28.66
Cable length	m ft	6 19.7	6 19.7











MW280-F

Inverter generator with integrated microprocessor.

Duty cycle

200 A (10 min/40°C.) 35% d.c.

145 A (10 min/40°C.) 60% d.c.

110 A (10 min/40°C.) 100% d.c.

Compact and lightweight, the **MW280-F** generator is offered by Maus Italia to control the **Giotto** series TIG welding orbital heads.

Available on "carriage pickUp" with cylinder holder and closeable compartment for housing the orbital head, the **MW280-F** generator is also ideal for on-site servicing.

It stands out due to the following features:

- Integrated water cooler with water control
- Intuitive touch-screen colour operating panel
- Multilingual
- Remote control with 10 m cable
- Routing of the current (welding, rotation axis, bleed gas and wire feed)
- Recording of imported heat energy
- USB port for transferring and recording data
- Integrated printer for welding data reports

MW280-F

Supply		
Mains voltage	Volt - Ph	230 - 3
Operating voltage	Volt	10,2 ÷ 18,0
Open-circuit voltage	Volt	44
Mains fuse	А	16
Cos phi		0,99
Welding current AC/DC (stepless)	Α	5 ÷ 200
Capacity		
Cooling power (on 40°C, 11/min)	w	500
Coolant capacity	I US gal	1,8 0.47
Coolant throughput (max.)	Vmin US gpm	3,0 0.79
Dimensions	- 1	
Length	mm inches	650 98
Width	mm inches	420 78
Hight	mm inches	1480 27
Weight	kg lbs	38 84
Colors	RAL	3020-9011
Degree of protection	IP	23





MAUS ITALIA S.P.A.

SP415 KM30 (nuova strada di arrocco) 26010 BAGNOLO CREMASCO (CR) ITALIA

Tel. +39 0373 2370 expo@mausitalia.it



