


Compatible Products	Connection Method	 CM-1029
<p align="center"><b>CM-900</b> Industrial CO2 Storage Safety 3 Alarm</p>	<p>The CM-1029 Strobe Siren will connect to the device by using the RJ45 Strobe Port of the device. A CAT5e Cable will be terminated to a (T-568B) RJ45 Connector to plug into the device. The other end of the CAT5e Cable will be spliced and will be hardwired to strobe screw terminals. Follow the diagram below and use the images for reference.</p>	
<p align="center"><b>RAD-0102-V6</b> Remote CO2 Storage Safety 3 Alarm</p>		
<p align="center"><b>RAD-0002-ZR</b> Oxygen Deficiency Safety Alarm</p>		



T-568B CAT5e Cable		CM-1029 Strobe
1	Brown	X - Not Used
2	White Brown	X - Not Used
3	Green	X - Not Used
4	White Blue	X - Not Used
5	Blue	GND
6	White Green	SIREN (+)
7	Orange	SIREN (+)
8	White Orange	GND
Add a jumper to Connect ( SIREN (+) and SIREN (+)		

