

Bring Your Beauty Salon Home

✉ service@melodysusie.com

🌐 <http://www.melodysusie.com>

📍 2809 Whipple Road, Union City, CA 94587

melodysusie

Aurora 2 LED Nail Lamp User Manual

Thank you for choosing MelodySusie! Please read this user guide carefully and keep it in an accessible location so you may refer to it later.

Items Included

1x MelodySusie Aurora 2 LED Nail Lamp
1x AC/DC adapter
1x User Manual

How to Use

Step 1: Connect the power cord to a grounded outlet.

Step 2: Select a pre-set timer button (30s, 60s, 90s or 30min) as needed.

Step 3: The LED bulbs will illuminate, and are now ready to cure gel polish. Note that the lamp will not turn on until you press one of the timer buttons.

Step 4: Place your hand in the nail lamp until the lamp turns off or your gel polish is cured.

Trouble Shooting

1. For best results, try to prevent extensive hand movement during curing.
2. Ensure that gel polishes are compatible with the Aurora 2 before you purchase them. The Aurora 2 is for gel polishes marked "LED" only.

Important Safety Information

1. Make sure your outlet supplies correct power voltage to avoid damage to the device.

2. Do not unplug the lamp during operation.
3. Always unplug the power cord in between use.
4. Do not place heavy objects on the lamp housing.
5. Do not disassemble the device. Doing so could be dangerous and constitutes voiding warranty conditions.
6. If the power cord is damaged, it should be replaced by MelodySusie or another authorized professional.
7. **WARNING:** Ultraviolet radiation may cause injury to eyes and skin. Protective UV shielding gloves are recommended.
8. Certain cosmetic substances may lead to adverse skin reactions.
9. Children under 18 years of age should not use this device without parental consent and supervision.

Warranty and Customer Service

This lamp has a 6-month limited warranty on quality related issues. **Please register on our website to extend your warranty and to view this manual in other languages.**

Aurora 2 Specifications

Weight: 1.5 lbs
Input: 100V-240V 50/60Hz
Size: 7.7 x 7.5 x 3.9 inches (LxWxH)