Technical Information



M-iClean UL

Execution for: Australia

Utensil washing machine

Alternating current: 1N PE 230V 50Hz Fresh water line: Soft warm water 0-3°dH



Sample illustration

Technical data

Rack capacity/h (theoretical)	40 / 30 / 15 racks/h
Programme cycle	90 / 120 / 240 s
Rack dimension	500 x 600 (500) mm
Entry height	435 mm
Dimensions (W x Hmin x D)	600 x 855 x 680 mm
Electrical feeding cable	Alternating current 1N PE 230V 50Hz*
	Total connected load: 2.7 kW
	max. rated current: 14.0 A
Local fuse protection	16 A
Protection class of the machine	IP X5
Equipment	Control system MIKE-CPU4
	Bluetooth interface for wireless communication
	Leakage detector
	Soft start
	Boiler safety device
	Automatic self-cleaning when tank is drained
	Roller base 35 mm
Fresh water line	Air gap 'AB' in accordance with EN 1717 with booster pump
Fresh water supply	Minimum flow pressure 60 kPa / 0.6 bar in front of solenoid valve
	Maximum pressure 500 kPa / 5.0 bar
	Max. supply water temperature 60 °C
Flow rate	4 I/min
Final rinse water quantity	2.8 liters/cycle, variable
Boiler	Contents: 7.9 I
	Heater: 2.00 kW
	Temperature: 83 °C
	Tank / boiler locked

M-iClean Page 1 / 2 MP000148718.1.1 M-iPlan 21/06/2017

Technical Information



Filling: 11.0 l
Heater: 2.00 kW
Temperature: 60 °C
Performance: 0.50 kW
Hose pump (24 V) with time control
and suction lance
Hose pump (24 V) with time control
and suction lance
Cladding: 1.4301
Wash tank: 1.4301
Boiler: 1.4571
for 20 programme cycles/h
total: 2.1 kW
perceptible: 1.4 kW
latent: 0.7 kW
540 m³/h
1.0 kg/h
62 dB(A)
79.0 kg / 91.5 kg (standard packaging)

*Note:

Electrical equipment suitable for supply voltage: 3N PE 400 V 50 HZ (3N PE 380-415 V 50 Hz) 1N PE 230 V 50 HZ (1N PE 220-240 V 50 Hz)

M-iClean Page 2 / 2 MP000148718.1.1 M-iPlan 21/06/2017