





Glaze Compatibility

105 Low Fire White and Low Fire White Casting Slip

We recommend both **bisque firing and glaze firing to cone 04 (1945°F)**. We have found that firing to cone 04 minimizes glaze defects or cloudiness in clear glazes.

Clear Glaze Compatibility

	LF2000 Clear	crystal clear at cone 04, cloudy in texture pools
	LG-10 Clear Transparent	crystal clear at cone 04, but may be slightly off color
	S-2101 Crystal Clear Brushing NT-BR Clear One Brushing NT-CLR Clear One Dipping Duncan PB001 Duncan IN1001	cloudy in texture pools, crystal clear at cone 04 slightly yellow, not compatible with some underglazes, may not fire glossy on LFW Slip slightly yellow, not compatible with some underglazes, may not fire glossy on LFW Slip crystal clear at cone 04, reacts well with underglazes slightly yellow, may blur crisp underglaze lines
	700 Clear	clearest glaze we've tested, reacts well with underglazes

Most underglazes are compatible. For best results when using a clear glaze, we recommend firing the underglaze on before applying clear glaze.

The list below includes glaze lines that we have either tested or that we know our customers have used with successful results. For glaze lines not listed, we recommend testing before use or contacting the glaze company directly.

	Lead-Free Low Fire (LF) Lead-Free Low Fire Dry (NL)
	Teacher's Palette (TP) Low Fire Gloss (LG) Velvet Underglaze (V) Liquid Underglaze (LUG)
	Foundations (FN) Elementals (EL)* Jungle Gems (CG)* Stroke & Coat (SC) Fundamentals (UG) Duncan Envisions
	700 Series Low Fire Opaque 500 Series Underglaze

*some colors may vary, we recommend testing beforehand