MINI MITO Open Fitting Models



This is the best solution for a customer who wants great performance and little dimensions, it's a battery 312 mini BTE. It supports an openfitting system or a bte system. It can be done in plus version with double receiver.





| | Mini Mito Basic | Mini Mito 8W2 | Mini Mito 8W4 | Mini Mito 16W6 | Mini Mito 16W8 |
|-----------------------|--------------------|------------------|------------------|-------------------|-------------------|
| WDRC Channels | 1 | 2 | 4 | 6 | 8 |
| Battery Type | 312 | 312 | 312 | 312 | 312 |
| Program Selector | • | • | • | • | • |
| Volume Control | - | - | - | - | - |
| i-Scene | - | - | - | • | • |
| Noise Reduction | - | - | - | • | • |
| Programmable Memory | 2 | 4 | 4 | 6 | 6 |
| Data Logging | - | - | - | • | • |
| Auto Fitting | • | • | • | • | • |
| Tinnitus Treatment | - | • | • | • | • |
| Feedback Canceller | • | • | • | • | • |
| Telecoil | - | - | - | - | - |
| Acoustic Indicators | • | • | • | • | • |
| Battery Life [hours]* | 260 | 260 | 260 | 250 | 250 |
| Performance | | | | | |

Accessories:

-Open Fitting System

-Ear Dome: OPEN, CLOSED

Accessories for Programming:

-Programming Cable (Hi-Pro)

Software:

Horentek Fitting

| OSPL 90 [Peak dB SPL] | 127 | 127 | 127 | 127 | 127 |
|-----------------------------|------|------|------|-----|-----|
| Full-On Gain [dB] | 44 | 44 | 44 | 44 | 44 |
| Harmonic Distortion | <3% | <3% | <3% | <3% | <3% |
| Battery Consumption [mA/h]* | 0.65 | 0.65 | 0.65 | 0.7 | 0.7 |

- Unvaiable

Available







Standard Colours





For more Technical Information visit www.horentekpro.com



^{*} Battery consumption was estimated according to the IEC 60118-7 a 1000Hz @ 65dB Data were obtained from tests conducted in accordance with the IEC 60118-7