



Press all three of the Pro-Click Buttons on the top of your Ion Orbit to turn each light on. Refer to th Lux 2.0 Display Modes insert for customizing each light. Hold the button to power off.





EC

3 START SPINNING



4 TENSION AND RELEASE A. After you have made a few big circles, pull the Orbit tight. This will cause the Orbit to spin fast in a small "orbit." The basic "orbit" motion may take a few tries, but it it is simply a matter of tension and release.

B. As the Orbit slows down, release tension. As it comes to a stop, pull the handles tight again to spin the Orbit in the opposite direction.

C. Repeat this process to continue the "orbit."

Grab one handle in each hand, and suspend the orbit in the air. Pull the Orbit fairly tight, with just a little bit of slack.



5 FLOWERS AND SHAPES To begin making more intricate shapes with your Orbit, simply combine steps 3 and 4. This will create a shape called a "flower." While the Orbit is spinning in it's "orbit", simultaneously spin the Orbit in big circles. This will create beautiful light patterns in front of your eyes.





BATTERIES

1 UNSCREW THE HOUSING Set your Orbit on a flat surface and use the included Phillips-head screwdriver to loosen the screw located in the middle of the Ion Orbit housing.





OPEN HOUSING & 2
REMOVE CHIPS








3 FRESH BATTERIES e the batteries out of each microchip. Replace patteries with two fresh CR1616 batteries. The side should face up toward the gold "X" clip.





FEATURES





- A ION HOUSING
- Made of lightweight polycarbonate
 Virtually indestructible
 Perfectly balanced
- B LUX 2.0 MICROCHIPS
 High Intensity LEDs with Brightness Control
 Virtually infinite color combinations
 Easy operation
 34 vibrant colors, 12 display modes
 Super bright
 Lock feature to preserve battery life
- T2 HANDLES

- Designed for unlimited tricks and superior control
 Create maximum tension
 No more blisters!

- (6) CR1616 BATTERIES C
 - Provides over 10 hours of battery life on any mode
 Up to 20 hours of battery life on practice modes
 Swap batteries hassle-free with the "X" clip
 - 2mm SATIN LEASHES Perfect for all styles of orbiting
 High-quality woven satin
 2mm diameter

SUPPORT SUPPORT@GLOFX.COM 844-GO-GLOFX (1-844-464-5639)