

PRODUCT DESCRIPTION

The BF GLAM series is composed of special thermoadhesive films coated with glossy polyester (PET) foil with a holographic finishing, free of PVC, plasticizers or heavy metals.

The cutting lines are highly visible, and the workability of the product is simple; its polyester adhesive carrier allows for fast weeding and easy repositioning of any small details that might have accidentally lifted from the carrier.

The blade integrity of the cutting plotter significantly determines the workability of the film.

APPLICATION TECHNIQUES

- Knockout
- Layering on other products

APPLICATION STEPS

- Cut - 45° blade
- Weed excess material
- Turn on your heat press - heat to 140°C/285°F
- Place your graphic on the garment
- Press it - 140°C/285°F for 12 seconds
- Remove the liner - hot

SIZES

H 50 cm	L 25 mt / 10 mt / 5 mt / 1 mt
H 75 cm	/
H 100 cm	/
H 150 cm	/

SAFETY NOTICE




The values reported in this document are average values as tested under normal conditions in our lab. We cannot provide a guarantee regarding the information abovementioned in this page. Due to possible variations in the production of garments, B-FLEX recommends testing the material prior to all applications.

Rev_2021/03






TECHNICAL DATA

	Film: PET/polyester
	Thickness: 90μ (±5%)
	Liner: adhesive PET
	Finish: gloss

PLOTTER SETTING

	Cut settings: mirror
	Blade: 45°
	Minimum cut: 0,5 cm

APPLICATION

	Temperature: 140°C - 285°F
	Time: 12''
	Liner removal: hot
	Pressure: medium - 3,5 bar - 50 PSI
	Textile: organic, synthetic, mixed

WASH RESISTANCE


First wash after application	wait 12 hours
Max wash temperature	40°C - 104°F
Dry clean	✗
Dryer	✗

BF GLAM


COLOUR GUIDE




- Holographic effect
- RAINBOW effect which contains four rainbow colors in the same film
- Don't fold after applied




BF L796A
SILVER GLAM




BF L792A
GOLD GLAM




BF L734A
ORANGE GLAM




BF L730A
RED GLAM




BF L750A
GREEN GLAM




BF L736A
PINK GLAM



BF L735A
LILAC GLAM



BF L738A
CYCLAMEN GLAM



BF L777A
RAINBOW GLAM

