

# New! Tricycle features



## Backrest angle

The backrest can be positioned vertically or at a 7½° or 15° recline.



## Carbon fiber drive belt

The drive belt will not rust or stretch, and will last at least five times longer than a bicycle chain.



## Variable pedal resistance

The adjustable brake can provide drag or lock the wheels for safe transfer.



## Seat depth

The seat depth adjusts easily with a knob underneath.

# New Tricycle features and benefits

## The new trike design offers a significant number of new or improved features

- **New** Weight limit for large size: 310 lbs. (old was 200 lbs. max)
- **New** The three sizes cover inside leg length range of 12"–38" (old was 17"–35")
- **New** Seat height adjusts on a low friction track. It can be adjusted while in use, depending on rider's weight and/or leg strength to aid in pushing up. Great for transfers.
- **New** Variable resistance braking system for slowing down riders who go too fast. Works great with the stationary stand (standard).
- **New** Front end and rear wheels remove for transport. Large trike fits easily in a minivan.
- **New** Carbon fiber drive belt – will not rust or stretch, and will last at least five times longer than a bicycle chain.
- **New** Laterals swing away for transfer. Independently adjustable for height, width and angle.
- **New** Pelvic harness, same as Activity Chair's (optional)
- **New** Backrest tilt: the backrest can be positioned vertically or at a 7½° or 15° recline (standard).
- **New** Adduction straps attach to rails on abductor (optional).
- **New** Caregiver brake, works with rear steer or push handle (optional).
- **New** Front basket (optional)
- **New** Hand anchors (pair) help riders who struggle to maintain their grip on the handlebars (optional).
- **New** Contoured, non-adjustable headrest (called contoured-fixed headrest)
- **New** Sandals can be removed to reveal standard bike pedal underneath. Heel stop on sandal.
- **New** Sandal straps – can be attached anywhere around the pedal, new long lasting Velcro
- **New** Pedal adjusts forward and backward on pedal crank to position rider's feet optimally.
- **New** Pedal raise kit – each block raises pedal by ½" (optional).
- **New** Mounting bar for attaching a third party phone / tablet holder – doesn't mount devices directly (optional)
- **New** All straps removable for Autism population.
- **New** Outdoor cover (optional)
- Push handle (optional)
- Rear steer – improved design without the bar that went around the user (optional)
- Parking brake (standard)
- Front hand brake – improved design with a locking/parking brake function (optional).
- Abductor – improved, now adjustable forward and back (optional).
- Front guide bar
- Stationary stand, transportable in rear basket

