







EAN:	4013288187949	Size:
Part number:	05057774001	Weight:
Article number:	Bit-Box 20 BTZ TX	Country of

Size:	75x68x20 mm
Weight:	125 g
Country of origin:	CZ
Customs tariff number:	82079030

- For TORX® socket screws
- BiTorsion zone to absorb peak loads
- · Considerable reduction in the risk of breakage, significant increase in service life
- Tough for hard materials
- 1/4" hexagon drive (Wera connecting series 4)
- Take it easy tool finder: colour coding according to profile and size
- In practical Bit-Box for simple removal

BiTorsion Bits for Phillips screws in a practical Bit-Box. Come with an elastic torsion zone where kinetic energy is diverted to when peak loads prevail and a softer BiTorsion zone to prevent the bit tip from twisting during peak loads: this significantly prolongs the product service life; with "Take it easy" Toolfinder: colour coding according to profile and size stamp; tough viscous design for universal use; 1/4" hex, suitable for holders as per DIN ISO 1173-D 6.3.



Bit-Box



The slide switch allows a simple and gradual removal and reinsertion of the bits. The transparent reverse side means that it is easy to know how many bits are still in the box.

BiTorsion Bits



Peak forces that occur in power tool applications often result in premature wear of bits or damage to the screw head. This usually occurs during initial power-up and the when the screw comes to a standstill. Screwdriving could become more productive and safer if these peak loads could be minimised. The Wera BiTorsion system prevents premature wear. The service life of the tool is extended and the productivity of tool applications power significantly increased.

Two cushioning torsion zones



The effectiveness of the BiTorsion system comes from a combination of two shock-absorbing spring elements. Both, bits as well as holders have a cushioning torsion zone that diverts the kinetic energy away from the drive tip during peak loads.

BiTorsion phase 1




The torsion spring integrated into the unique BiTorsion holder absorbs lower levels of peak loads (Phase 1). Any overloading of this spring is effectively prevented by means of a supporting mechanism.

BiTorsion phase 2



Higher peak loads are minimised through the torsion effect of the bit shaft (Phase 2).

Above-average service life



Even the service life of conventional bits is enhanced with the use of the BiTorsion holder and the BiTorsion bit also functions in a normal holder.

BiTorsion and conventional tools



The BiTorsion holder and the BiTorsion bit can, of course, be used independently of one another.

Web link



Set contents:



20x TX 25 x 25 mm



Wera - Bit-Box 20 BTZ TX 05057774001 - 4013288187949 Wera Werkzeuge GmbH Korzerter Straße 21-25 D-42349 Wuppertal Tel: +49 (0)2 02 / 40 45-0 E-Mail: info@wera.de