


SUGGESTED - PRINT PANEL AREA

GUIDE ONLY. Prior to artwork, and other costs, it is imperative to confirm with your chosen printer that this guide & sizing is suitable for your use.

Note: All dimensions and tolerances are subject to final product specification.



	TOLERANCE	1			Vision Packaging (Aust.) Pty Lin	nited 16 075 725 576	DATE: 16/07/2019
	0mm-15mm						
	15mm-30mm	±0.05	±0.15	±1.00	NAME: Airless Jar 50mL Ava Base + APJY Airless Lotion Pump with Overcap		
	30mm-50mm	±0.10	±0.20	±1.50	DRAWING ID: 156avajarbase0050-JY165 + 156avajarlid0050-JY165		
	50mm-99mm	±0.15	±0.30	±2.00	DIVAVVIIVO ID. 130avajarbase0030-31	100 + 100avajaniu0000-	01100
	> 99mm	±0.20	±0.40	±2.50	NOMINAL FILL: 50mL	BRIMFUL CAPACITY:	72.0 \pm 5.0mL
	CENTER	±0.10	±0.50	±1.00	VISUAL ANGLE:		LIMIT
6	ANGLE	±0.25°	±0.50°	±2.00°	VISUAL ANGLE		UNIT: mm

NOT DRAWN TO SCALE
Please SIZE and SUPPLY Artwork to 100%