

Kimba buggy

Discover the world safely and conveniently



The Kimba buggy has been upgraded and improved by users, therapists and doctors jointly. The focus was on safety, quality, individuality and comfort. The new Kimba features an airy design, extra storage space and various enhancements in day-to-day handling. It remains the ideal companion for trips to the nursery and supermarket or in the car.

Key features

- Available in two sizes
- Frame colours: black or white
- Padding colour: grey
- Frame made of high-quality aluminium
- Seat tilt up to 40°
- Height-adjustable push bar with ratchet joint
- Swivelling front wheels
- EVA wheels with wheel lock
- Integrated anchor brackets for transportation in a vehicle for transporting persons with reduced mobility
- Kimba seat adapter, also suitable for custom seating shell systems
- Generous storage space under the seat (also usable as a platform for respirators)
- Optimised rear axle suspension
- Automatic folding lock for safely loading the outdoor mobility base into a vehicle



• Kimba seating unit



• Kimba outdoor mobility base

Options

- Padding in four different colours
- Safety cord
- Reflective colour accents (Class RA1 reflective)
- Impact protection
- "Techno" buggy board
- Seating shell interface with foot support assembly
- Drum brake
- Foot support assembly for seating shell interface
- Nappy bag
- Tip-assist: left or right
- Tray
- Pneumatic tyres



Inlay colors



Self-reflective stickers



Technical data	Size 1	Size 2
Overall width	595 mm	665 mm
Front/rear wheel diameter	170/280 mm	170/280 mm
Push handle (min./max.)	710–1,160 mm	710–1,160 mm
Folding size without seat (LxWxH)	790x595x460 mm	790x665x460 mm
Min. folding size with seat facing forward (LxWxH)	900x595x530 mm	970x665x590 mm
Seat tilt (min./max.)	-40° to +10° or -10° to +40°	-40° to +10° or -10° to +40°
Weight of outdoor mobility base	10.5 kg	11.5 kg
Weight of seating unit	7.5 kg	9.5 kg
Max. load, seating unit*	40 kg	40 kg
Max. load, storage basket*	15 kg	15 kg
Max. load, outdoor mobility base	55 kg	55 kg

*The maximum permissible overall weight of the user and load in the storage basket is 47.5 kg (size 1) or 45.5 kg (size 2).




NEW

Uncomplicated, safe adjustment of back support angle with a locking pin.



NEW

New inlays – customised and hygienic.



NEW

Generous storage space under the seat. Can also be used as a platform for respirators.



NEW

Tilt activation is positioned close by on the push bar for very convenient operation.



NEW

Easy to fold, including automatic folding lock



NEW

Self-reflective stickers in two variants are available to match the inlays.

i You may request the instructions for use with comprehensive information on the product as a PDF file at the email address orders@ottobock.com.au. The PDF file can also be displayed in a larger size.