Sampling Filter by Atrix



VERSATILE

Any vacuum, collect whatever dust, dirt, or insect that needs identification

EASY TO USE

Simply place between choice of attachment and vacuum hose (for VACBP1 and VACBP36V use adapter ATI34663 - which reduces diameter from 1.38" to 1.25")

COLLECT AND CONTAIN

Collect, seal, and label for lab use

APPLICATIONS

Hazardous Particulate, Pest Control, Bulk Sampling Identification

The ATISF-U15 is an economical and highly efficient single use disposable dust sampling filter manufactured with U15 PTFE (99.9995% Efficiency) Filtration Media, and has been independently tested to exceed HEPA (99.97% efficiency at .3 Micron) Efficiency.



Determine Resistance



Sampling Filter by Atrix

9/5/17

B. Miller

Ink/pencil friendly label

SPECIFICATIONS

SFU15/6

Sold as set of 6

DIMENSIONS

Overall Length: 5.10" (129.5 mm) Diameter: 3.06" (77.7 mm)

Intake (Utensil) End: 1.07" I.D., 1.21" O.D. 27.18 mm I.D., 30.73 mm O.D.

Exhaust (Hose) End: 1.24" I.D., 1.50" O.D 31.49 mm I.D., 38.1 mm O.D.

Housing: ABS



1.5" - 38 mm diameter (fits outside)

The ATISF-U15 is an economical and highly efficient single use disposable dust sampling filter manufactured with U15 PTFE (99.9995% Efficiency) Filtration Media, and has been independently tested to exceed HEPA (99.97% efficiency at .3 Micron) Efficiency.

The ATISF-U15 features two strips of tape for the users to mark, date and label sampling contents prior to sending to the lab for content analysis as well as a plug to seal in the sample material for safe transport and storage. In addition, the ATISF-U15 is only 5" long and 3" in diameter and is manufactured with a clear ABS housing for visual analysis of the sampling contents.

The ATISF-U15 single use disposable dust sampling filter has been designed and engineered to be able to be used with most vacuum cleaners as it has a hose end receptacle that is 1.24" I.D. and 1.50" O.D. The utensil end measures 1.07" I.D. and 1.21" O.D. and is designed and engineered to accept Atrix Omega Series utensils, such as the **730030** crevice tool or **AVPA011** utility tool, among others. If using an ERGO vacuum the ATI34663 adapter must be used.

This new economical, single use disposable and highly efficient dust sampling filter has up to a 6 oz. capacity (dependent on particle size) and will be an excellent aid to environmental consultants, scientists, lab technicians, pest control technicians, entomologists, industrial hygienists, occupational hygienists for hazardous dust (such as astesbos) sampling collection and even homeowners who need to sample lead dust or mold for analysis by trained professionals. The uses for the Atrix ATISF-U15 are varied and unlimited.

GENERAL INFORMATION

Packaging (6 pack)			
Dimensions:	L	W	Н
Inches:	12.5	6.5	5.88
mm:	318	165	149
Weight:	1.70 lbs.		
	.77 kg		

HS Code

Removable Plug

5911.90.0000

UPC

8 38067 00321 0

Use With Any Atrix Vac (examples)



VACBP1



VACOMEGASIPM



VACBP36V