

CERTIFIED FIRE-**RESISTANT** FILING CABINET **FOR PROFESSIONAL STORAGE OF YOUR IMPORTANT DOCUMENTS**





FIRE RESISTANT DOCUMENT PROTECTION



KEY FEATURES

- Certified for one hour's fire protection of documents in accordance
- Maximised storage capacity allowing users to gain full advantage for
- Chubbsafes Fire File 25" is available with two or four drawers
- Easy to operate day catch to secure the drawers when closed.
 Units do not have to be locked to provide fire protection, they just have to be pushed closed
- High-quality steel sliders to ensure comfortable operation and full drawer access
- Lighter weight construction which means smoother transportation
- All models fitted with a single key lock as standard
- Alternative locking options available at additional costs
- Light grey, powder-coated finish and modern design which blends
- Chubbsafes Fire File 25" is manufactured in accordance with ISO 9001 for quality management systems and ISO 14001 for environmental management systems



Model	External height (mm)	External width (mm)	External depth* (mm)	Internal height (mm)	Internal width (mm)	Internal depth (mm)	Capacity (litres)	Weight (kg)
2 drawers	784	551	635	290	387	460	104	164
4 drawers	1510	551	635	290	387	460	208	291

^{*}Projection of handle (35mm) not included

LOCK OPTIONS



Chubbsafes Fire File 25" models are fitted with a single key lock as standard. They can be equipped with a mechanical combination lock for dual locking on request. In addition a key lock can be fitted to each drawer for an independent locking option.

All non-standard locking options are available with an extended lead time and at an additional cost



FINISH

Color: Light Grey RAL 7035

Authorised dealer

FIRE TESTING

Chubbsafes Fire File 25" cabinets are tested and certified in accordance with the most common and well established UL (Underwriter's Laboratories) Standard 72 to Class 350 for 1 hour fire endurance. The products are subjected to extensive fire testing which simulates the impact of a severe fire. This two-step process includes the following:

STEP 1

The filing cabinet is placed in a furnace and heated to a temperature of 1000°C. The furnace is switched off after one hour. The unit remains in the furnace until the temperature returns to ambient levels. The content is then examined for signs of damage. Both during furnace heating and the subsequent cooling period, the recorded internal temperature must not have exceeded 177°C (or 350°F).

STEP 2

Fire explosion or Shock test. To simulate sudden heating, possibly as a result of rapid fire spread, the cabinet is inserted into a preheated furnace. The stresses and strains created by such rapid heating can easily cause a poorly constructed unit to fail. At no point are internal temperatures allowed to exceed those specified for the fire endurance test in Step 1.

www.chubbsafes.com



The data given in this material may be subject to change without prior notice. This document is not contractually binding. The 'Chubb' brand is owned by Chubb plc and is a registered trademark used under license. See www.chubbsafes.com for more information.