

ATOM

FOR HEALTHCARE PROFESSIONALS

ATOM goggles combine ultimate protection and comfort to help reduce workplace accidents. Equipped with **Platinum® anti-scratch & anti-fog coating** applied on both sides of the lens, ATOM ensures long-lasting comfort, performance and reliability. Suitable for healthcare industry.

✦ **PLATINUM®**



1652801 • Clear Indirect Vents
1652821 • Clear Top Vent Closed



72 g





- + LOW PROFILE AND LIGHTWEIGHT PVC FRAME WITH A SPHERICAL POLYCARBONATE LENS OFFERING BRILLIANT PERIPHERAL VISION**
- + ✦ PLATINUM® ANTI-SCRATCH & ANTI-FOG COATING (✦)**
- + MEDIUM IMPACT AND CHEMICAL SPLASH PROTECTION APPROVED**
- + ADJUSTABLE STRAP**

bolle
SAFETY

ATOM

FOR HEALTHCARE PROFESSIONALS

MODEL	VERSIONS	PRODUCT CODE	LENS MARKING	FRAME MARKING	COATINGS
ATOM	 Clear Indirect Vents	1652801	CIO	AS/NZS 1337.1:2010	Anti-scratch/Anti-fog / [†] P
	 Clear Top Vent Closed	1652821	CIO	AS/NZS 1337.1:2010	Anti-scratch/Anti-fog / [†] P

LENS MARKING

- [†]P. Platinum is a permanent coating applied on both sides of the lens that gives a high resistance to scratching (1.4 cd / m²) and to the most aggressive chemicals and delays the onset of fogging for two minutes, as per the testing requirements of EN166.
- C. The letter 'C' signifies that the product has been tested and approved for use against splashes and is appropriate for chemical handling.
- I. The letter 'I' signifies 'Medium Impact' approval.
- O. The letter 'O' signifies that the product has been approved for the use both outdoors and indoors, and the terminology used by Australian standards is 'outdoor un-tinted'. This marking appears on all clear, amber and contrast lenses.

Ocular lens category:

- O. Range of luminous transmittance 80–100% (Clear).

TECHNOLOGIES

PLATINUM

The exclusive scratch and fog resistant PLATINUM® coating guarantees even more safety, reliability and comfort. Washable (water and soap), this permanent coating applied on both sides of the lens makes it highly scratch resistant and durably delays the appearance of fogging.

LENSES

- 2mm polycarbonate
- Platinum coating on both sides of Clear lens
- 99.9% UV 385 – Clear

FRAME MARKING

AS/NZS 1337.1:2010 : Tested and approved to AS/NZS 1337.1:2010 for medium impact protection. Resists a 6mm ball at 45 m/s.

CLEANING AND STORAGE

CLEANING: The lenses should be cleaned regularly. Bollé Safety recommends only using the B-clean lens cleaning system.

MAINTENANCE: Pitted, scratched or damaged lenses must be replaced by replacing the complete product. If the frame is damaged also replace the complete product. After each use it is recommended to keep the spectacles or goggles in a microfiber pouch or rigid case.

STORAGE: All products must be stored in a dry and clean environment.

Always read and follow the instructions on the label.

CHARACTERISTICS

LENSES	Polycarbonate
FRAME	PVC
TEMPLES	Non Applicable
STRAP	Yes
FOAM	Yes
SPARE LENSES	No



Non-contractual pictures
26/05/2021

ASIA/PACIFIC HEADQUARTERS:

Bollé Safety AU Pty Limited
32–40 Fairchild Street
Heatherton VIC 3202
T: 1300 138 098
E: sales@bollesafety.com.au

bollesafety.com.au

NEW ZEALAND:

T.: 0800 2655 369
E: sales@bollesafety.com.au

bolle
SAFETY