


CDK20 and 24 - OPTICAL TRAIN: FINGERLAKES CAMERA'S AND FILTER WHEELS



FLI ProLine Camera Body	8.81	remaining BF
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.62	5.19
3.5" to SecureFit, 3.8" - 200361-1	3.8	1.39
SecureFit to FLI 3" Threads - 200395	0.25	1.14
FLI ProLine Camera	1.14	0

Using the Rotating Focuser 600180

FLI ProLine Camera Body	8.81	remaining BF
3.5" Focuser (racked in)	0.82	7.99
Focus position (0 to 1.3")	0	7.99
3.5" to SecureFit, 2.1" - 200361-2	2.1	5.89
SecureFit 1/2" Extender - 200377	0.5	5.39
SecureFit 1/2" Extender - 200377	0.5	4.89
SecureFit to FLI 3" Threads - 200395	0.25	4.64
FLI ProLine Camera	1.14	3.5

FLI ProLine Camera Body and CFW5 filter wheel	8.81	remaining BF
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.882	4.928
3.5" to SecureFit, 2.1" - 200361-2	2.5	2.428
SecureFit CCD Extender - 200377	0.5	1.928
SecureFit to FLI 3" Threads - 200395	0.25	1.678
FLI CFW5 Filter Wheel	0.848	0.83
FLI ProLine Camera	0.83	0

Using the Rotating Focuser 600180




FLI ProLine Camera Body and CFW5 filter wheel	8.81	remaining BF
Rotating Focuser (racked in)	3.5	5.31
Focus position (0 to 1.3")	0.382	4.928
3.5" to SecureFit, 2.1" - 200361-2	2.5	2.428
SecureFit CCD Extender - 200377	0.5	1.928
SecureFit to FLI 3" Threads - 200395	0.25	1.678
FLI CFW5 Filter Wheel	0.848	0.83
FLI ProLine Camera	0.83	0

FLI ProLine Camera, CFW5 filter wheel & MonsterMOAG	8.81	remaining BF
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.582	5.228
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.728
SecureFit CCD Extender - 200377	0.5	4.228
Adapter SecureFit to Monster MOAG - 200394	0.55	3.678
Monster MOAG - MMOAG	1.25	2.428
AstroDon Adapter to 3" - 24 threads x .75" (MMOAG-3-L)	0.75	1.678
FLI CFW5 Filter Wheel	0.848	0.83
FLI ProLine Camera	0.83	0


FLI ProLine Camera, CFW4 filter wheel & MonsterMOAG	8.81	remaining BF
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.395	5.415
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.915
SecureFit CCD Extender - 200377	0.5	4.415
Adapter SecureFit to Monster MOAG - 200394	0.55	3.865
Monster MOAG - MMOAG	1.25	2.615
AstroDon Adapter to 3" - 24 threads x .75" (MMOAG-3-L)	1	1.615
FLI CFW4 Filter Wheel	0.785	0.83
FLI ProLine Camera	0.83	0

Using the Rotating Focuser 600180

FLI ProLine Camera, CFW5 filter wheel & MonsterMOAG	8.81	remaining BF
Rotating Focuser (racked in)	3.5	5.31
Focus position (0 to 1.3")	0.582	4.728
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.228
Adapter SecureFit to Monster MOAG - 200394	0.55	3.678
Monster MOAG - MMOAG	1.25	2.428
AstroDon Adapter to 3" - 24 threads x .75" (MMOAG-3-L)	0.75	1.678
FLI CFW3 or 5 Filter Wheel	0.848	0.83
FLI ProLine Camera	0.83	0



CDK20 and 24 - OPTICAL TRAIN: FINGERLAKES CAMERA'S AND CENTERLINE FILTER WHEELS



FLI ProLine Camera Body and CL1-10 filter wheel		8.81 remaining BF
3.5" Focuser (racked in) -200340	3	5.81
Focus position (0 to 1.3")	0.53	5.28
3.5" to SecureFit, 2.1" - 200361-2	2.1	3.18
SecureFit CCD Extender - 200377	0.5	2.68
SecureFit CCD Extender - 200377	0.5	2.18
SecureFit to FLI Centerline CFW - 200395-CL	0.25	1.93
FLI CL1-10 Filter Wheel	1.1	0.83
FLI ProLine Camera	0.83	0

Using the Rotating Focuser 600180		8.81 remaining BF
FLI ProLine Camera Body and CL1-10 filter wheel	8.81 remaining BF	
Rotating Focuser (racked in) -600180	3.5	5.31
Focus position (0 to 1.3")	0.53	4.78
3.5" to SecureFit, 2.1" - 200361-2	2.1	2.68
SecureFit CCD Extender - 200377	0.5	2.18
SecureFit to FLI Centerline CFW - 200395-CL	0.25	1.93
FLI CL1-10 Filter Wheel	1.1	0.83
FLI ProLine Camera	0.83	0

FLI ProLine Camera, CL1-10 filter wheel & MonsterMOAG		8.81 remaining BF
3.5" Focuser (racked in)	3	5.81
Focus position (0 to 1.3")	0.63	4.98
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.48
SecureFit CCD Extender - 200377	0.5	3.98
Adapter SecureFit to Monster MOAG - 200394	0.55	3.43
Monster MOAG - MMOAG	1.25	2.18
AstroDon 3"-24 male thread, 0.4" - MMOAG-3-M	0.4	1.78
FLI CL Zero Tilt Adapter to 3"-24 female thread -AD-72	0.15	1.63
FLI CL1-10 Filter Wheel	1.1	0.53
FLI ProLine Camera	0.83	0

Using the Rotating Focuser 600180		8.81 remaining BF
FLI ProLine Camera, CL1-10 filter wheel & MonsterMOAG	8.81 remaining BF	
Rotating Focuser - 600180 (racked in)	3.5	5.31
Focus position (0 to 1.3")	0.53	4.78
Low Profile SecureFit Spacer - 600327 and 600328	0.5	4.28
Adapter SecureFit to Monster MOAG - 200394	0.55	3.73
Monster MOAG - MMOAG	1.25	2.48
AstroDon 3"-24 male thread, 0.4" - MMOAG-3-M	0.4	2.08
FLI CL Zero Tilt Adapter to 3"-24 female thread -AD-72	0.15	1.93
FLI CL1-10 Filter Wheel	1.1	0.83
FLI ProLine Camera	0.83	0

