

Smart UV Portable UV-C Sterilization Lamp

Instruction Manual



Product Specifications

Product Name: Smart UV - Portable UV-C Sterilization Lamp
Power: 2.5 Watts
Input Voltage: 3.7 Volts
Product Size: 14.1 x 6.2 x 5.2cm
Recharging Plug Type: MicroUSB
Range: 4.5ft/20 square feet

Product Details

1. UV-C Emitting Bulb
2. 30 Second Delay ON Button
3. Protective Outer Shell
4. Maneuverable Stand



Best Practices & Safety Protocols

1. Keep out of reach from children. During use, do not touch the lamp body or have direct contact with the UV-C light on skin, animals, or plants. Precious painting materials should not be present.
2. Before turning on Smart UV, please close all doors and windows. After turning on The Smart UV please leave the room. Enclosing the room helps the sterilization process. After sterilization, we recommend ventilating the room by opening the doors and windows.
3. In case of a malfunction or control failure of Smart UV, or an emergency shut off is needed - cover up with long sleeves and cover the face and wear UV-C protective eyeglasses. Then enter the room and press and hold the power button until shut off. In the case of a malfunction please reach out to the Smart UV team to go over your warranty.
4. When The Smart UV is not in use, please place in a dry environment to ensure the health of your product.

WARNING

When turning on the light, please leave the room. You can not be in the room during operation. UV-C light is dangerous to people, pets, and plants. Please use with care.

General Instructions

Press and hold the power button for 3 seconds to turn Smart UV on or off.

After turning Smart UV on, the power button will flash for 30 seconds and the sterilization will start.

After 30 minutes Smart UV will automatically shut off.

When charging Smart UV, the power button will turn from red to green when fully charged.

Smart UV
hi@smartuv.shop
www.smartuv.shop