


450

Light Transmittance: 71%



Spectrophotometry Graph



450x

Light Transmittance: 74%



Spectrophotometry Graph




450XG

Light Transmittance: 38%



Spectrophotometry Graph




511

Light Transmittance: 45%



Spectrophotometry Graph




511X

Light Transmittance: 50%



Spectrophotometry Graph




527

Light Transmittance: 33%




Spectrophotometry Graph




527X

Light Transmittance: 39%



Spectrophotometry Graph




550

Light Transmittance: 20%




Spectrophotometry Graph




550XD

Light Transmittance: 8%



Spectrophotometry Graph




GLC (CPF Glare Cutter Simulation)

Light Transmittance: 19%



Spectrophotometry Graph



Noir #81 20% Plum

Light Transmittance: 19%



Spectrophotometry Graph



Noir #88 40% Light Plum

Light Transmittance: 57%



Spectrophotometry Graph

