AT-E2CMKII **Battery Adaptor for CANON C300 MKII**



EOS C Series (As of September, 2015)

C300 Mark II

Instruction Manual

Thank you for purchasing the AT-E2CMKII. AT-E2CMKII is specifically designed for interfacing ENDURA batteries to CANON's EOS C300 Mark II camera. Prior to using the AT-E2CMKII, IDX strongly recommends reading this Instruction Manual on how to best use the AT-E2CMKII. We recommend keeping this manual for your reference. If you have any additional questions, please contact your local IDX office listed at the end of this manual.

Specifications

- DC output
- D-Tap output voltage

: Battery through voltage (D-Tap1, D-Tap2) Maximum load : 50W(per D-Tap)

- Ambient temperature $:32 \sim 104^{\circ}F(0 ~^{\circ}C \sim 40^{\circ}C)$
- DC cable length : 300mm / 12inches
- Dimensions / Weight

:82.5(W) × 142(H) × 12(D)mm / 210g

: DC16.8~12V / Max10A (Max 120W)

- : 3.25(W) × 5.59(H) × 0.47(D)inches / 0.46lbs Accessories : Installation manual x 1, M3 (8mm)screw x 4
- * Please keep in mind that the total discharge must be within battery specification.

Installation

(1) Install the AT-E2CMKII to an applicable plate by using the supplied screws. Ensure that all four screws are tightly fastened.

(2) Attach the ENDURA battery then connect the DC cable to camera.

<For example>



General Notes and Safety

- Please remove battery after use.
- Do not apply strong tension to the DC cable when pluging and unpluging
- Do not short circuit between plus(+) and minus(-) pins.
- Do not attempt to open or modify this unit. All work should be carried out by IDX authorized service personnel only.
- Make sure that the adaptor and battery are tightly fastened to the equipment, otherwise it may cause damage or even injury
- Stop using immediately in case of abnormal smell, visible leak, color change or physical deformity during operation.
- When inspection or repair is needed, please contact your local IDX office listed at the end of this manual.



Designs and specifications are subject to change without notice.

IDX Company, Ltd. : 6-28-11 Shukugawara, Tama-ku, Kawasaki-shi, Kanagawa-ken 214-0021 Japan Tel : +81-44-850-8801 Fax : +81-44-850-8838 E-mail : idx.japan@idx.tv IDX System Technology, Inc.: 19001 Harborgate Way, Suite 105, Torrance, CA 90501 USA Tel:+1-310-328-2850 Fax:+1-310-328-8202 E-mail:idx.usa@idx.tv IDX Technology Europe, Ltd. : Unit 9, Langley Park, Waterside Drive, Langley, Berkshire SL3 6EZ England Tel:+44-1753-547-692 Fax:+44-1753-546-660 E-mail:idx.europe@idx.tv

