### **Technical Data Sheet**

### **DOWTHERM™ SR-1 Fluid**

**Product Type** 

Inhibited Ethylene Glycol-based heat transfer fluid

### **Applications**

- Closed-loop, water-based HVAC
- Process heating and cooling
- Food industry applications within temperature range

Recommended Use Temperature Range

-50°C (-60°F) to 120°C (250°F)

### **Description**

DOWTHERM SR-1 heat transfer fluid is a formulation of 95.5 weight percent ethylene glycol and a specially designed package of industrial corrosion inhibitors. The fluid is dyed fluorescent pink for leak detection purposes. Solutions in water provide freeze protection to below -50°C (-60°F) and burst protection to below -73°C (-100°F).

# Typical Properties<sup>†</sup>

### Composition (% by weight)

Ethylene Glycol	95.5
Performance Additives	4.5
Color	Fluorescent pink
Specific Gravity 25/25°C (77/77°F)	1.1250-1.1350
pH of Solution (50% glycol)	9.0-10.5
Reserve Alkalinity (min.)	12.0 ml

<sup>&</sup>lt;sup>†</sup>Typical properties, not to be construed as specifications. Complete sales specifications are available on request.

## Typical Concentrations of DOWTHERM SR-1 Fluid Required to Provide Freeze and Burst Protection at Various Temperatures

Tempe	erature	Percent DOWTHERM SR-1 Fluid Concentration Required					
°C	(°F)	For Freeze Protection Volume %	For Burst Protection Volume %				
-7	(20)	16.8	11.5				
-12	(10)	26.2	17.8				
-18	(0)	34.6	23.1				
-23	(-10)	40.9	27.3				
-29	(-20)	46.1	31.4				
-34	(-30)	50.3	31.4				
-40	(-40)	54.5	31.4				
-46	(-50)	58.7	31.4				
-51	(-60)	62.9	31.4				

**Note:** These figures are examples only and may not be appropriate to your situation. Generally, for an extended margin of protection, you should select a temperature in this table that is at least 3°C (5°F) lower than the expected lowest ambient temperature. Inhibitor levels should be adjusted for solutions of less than 30% glycol. Contact Dow for information on specific cases or further assistance.

Attention: These are typical numbers only and are not to be regarded as specifications. As use conditions are not within its control, Dow does not guarantee results from use of the information or products herein; and gives no warranty, express or implied.

Typical Freezing and Boiling Points of DOWTHERM SR-1 Fluid<sup>†</sup>

Wt. % Ethylene Glycol	Vol. % Ethylene Glycol	Wt. % DOWTHERM SR-1	Vol. % DOWTHERM SR-1	Freezing Point		Boiling Point °C @ 101 kPa (°F @ 760		Degree Brix <sup>††</sup>	Refractive Index 22°C
	•			°C	(°F)	mmHG)			(72°F)
0.0	0.0	0.0	0.0	0	(32.0)	100.0	(212)	0.0	1.3328
5.0	4.4	5.2	4.6	-1.4	(29.4)	100.6	(213)	3.8	1.3378
10.0	8.9	10.5	9.3	-3.2	(26.2)	101.1	(214)	6.8	1.3428
15.0	13.6	15.7	14.2	-5.4	(22.2)	101.7	(215)	9.9	1.3478
20.0	18.1	20.9	19.0	-7.8	(17.9)	102.2	(216)	13.0	1.3530
25.0	22.9	26.2	24.0	-10.7	(12.7)	103.3	(218)	16.1	1.3582
30.0	27.7	31.4	29.0	-14.1	(6.7)	104.4	(220)	19.2	1.3635
35.0	32.6	36.6	34.1	-17.9	(-0.2)	105.0	(221)	22.3	1.3688
40.0	37.5	41.9	39.3	-22.3	(-8.1)	105.6	(222)	25.3	1.3741
45.0	42.5	47.1	44.5	-27.5	(-17.5)	106.7	(224)	28.3	1.3796
50.0	47.6	52.4	49.8	-33.8	(-28.9)	107.2	(225)	31.2	1.3849
55.0	52.7	57.6	55.2	-41.1	(-42.0)	108.3	(227)	33.9	1.3900
60.0	57.8	62.8	60.5	-48.3	(-54.9)	110.0	(230)	36.6	1.3952
65.0	62.8	68.0	65.8	а	а	112.8	(235)	39.1	1.4003
70.0	68.3	73.3	71.5	а	а	116.7	(242)	41.7	1.4055
75.0	73.6	78.5	77.1	а	а	120.0	(248)	44.2	1.4107
80.0	78.9	83.8	82.6	-46.8	(-52.2)	123.9	(255)	46.6	1.4159
85.0	84.3	89.0	88.3	-36.9	(-34.5)	133.9	(273)	49.0	1.4208
90.0	89.7	94.2	93.9	-29.8	(-21.6)	140.6	(285)	51.2	1.4255
95.0	95.0	99.5	99.5	-19.4	(-3.0)	158.3	(317)	53.2	1.4300

<sup>&</sup>lt;sup>†</sup>Typical properties, not to be construed as specifications.

NOTE: Generally for an extended margin of protection, you should select a temperature in this table that is at least 3°C (5°F) lower than the expected lowest ambient temperature. Inhibitor levels should be adjusted for solutions of less than 30% glycol. Contact Dow for information on specific cases or further assistance.

Saturation Properties of DOWTHERM SR-1 Fluid at 30% Ethylene Glycol Concentration by Volume

Temperature Specific Heat Density Therm. Cond. Viscosity										
	erature	Specific Heat				Therm. Cond.		Viscosity		
°C	(°F)	kJ/(k	kJ/(kg)(K) kg/m³ W/mK		mK	mPa•s				
	` ,		b. °F)	(lb./	ft.3)	[Btu/hr. ft.2 (°F/ft.)]		(cps)		
-10	(14)	3.562	(0.851)	1055.47	(65.89)	0.4154	(0.2400)	6.1788	(6.18)	
10	(50)	3.619	(0.865)	1049.91	(65.54)	0.4420	(0.2554)	2.9482	(2.95)	
40	(104)	3.704	(0.885)	1037.92	(64.80)	0.4731	(0.2733)	1.3398	(1.34)	
65	(149)	3.775	(0.902)	1024.59	(63.96)	0.4909	(0.2836)	0.8246	(0.82)	
90	(194)	3.846	(0.919)	1008.20	(62.94)	0.5015	(0.2897)	0.5599	(0.56)	
120	(248)	3.931	(0.939)	984.53	(61.46)	0.5044	(0.2915)	0.5044	(0.38)	

Saturation Properties of DOWTHERM SR-1 Fluid at 40% Ethylene Glycol Concentration by Volume

	erature	Specif	ic Heat	Den	sity	Therm	. Cond.	Visc	osity	
°C	(°F)			kJ/(kg)(K) kg/m³				mK	mPa•s	
		(Btu/l	b. °F)	(lb./	(lb./ft.³) [Btu/hr. ft.² (°F/ft.)]		.² (°F/ft.)]	(cps)		
-20	(-4)	3.336	(0.797)	1073.23	(67.00)	0.3707	(0.2142)	15.7533	(15.75)	
10	(50)	3.436	(0.821)	1064.73	(66.47)	0.4053	(0.2342)	4.0451	(4.05)	
40	(104)	3.537	(0.845)	1051.85	(65.66)	0.4312	(0.2491)	1.7731	(1.77)	
65	(149)	3.621	(0.865)	1037.76	(64.79)	0.4462	(0.2578)	1.0646	(1.06)	
90	(194)	3.705	(0.885)	1020.63	(63.72)	0.4552	(0.2630)	0.7013	(0.70)	
120	(248)	3.805	(0.909)	996.06	(62.18)	0.4582	(0.2647)	0.4614	(0.46)	

th Degree Brix is a measure of the sugar concentration in a fluid and is important in fermentation and syrups applications. Although there is no sugar present in DOWTHERM heat transfer fluids, the glycol affects the refractive index of the fluid in a similar fashion.

aFreezing points are below -50°C (-60°F).

Saturation Properties of DOWTHERM SR-1 Fluid at 50% Ethylene Glycol Concentration by Volume

Temp	erature	Specific Heat		Den	sity	Therm	. Cond.	Viscosity	
°C	(°F)	kJ/(kg)(K)		kg/m³		W/	mK	mP	a•s
		(Btu/lb. °F)		(lb./	/ft.³)	t. <sup>3</sup> ) [Btu/hr. ft. <sup>2</sup> (°F/ft.)		(c	os)
-30	(-22)	3.090	(0.739)	1090.31	(68.07)	0.3333	(0.1926)	43.9970	(44.0)
-20	(-4)	3.129	(0.748)	1088.15	(67.93)	0.3442	(0.1989)	22.0816	(22.08)
10	(50)	3.245	(0.776)	1078.72	(67.34)	0.3724	(0.2152)	5.5071	(5.51)
40	(104)	3.361	(0.803)	1064.91	(66.48)	0.3937	(0.2275)	2.2567	(2.26)
65	(149)	3.457	(0.826)	1050.05	(65.55)	0.4062	(0.2347)	1.2936	(1.29)
90	(194)	3.554	(0.849)	1032.15	(64.44)	0.4139	(0.2391)	0.8227	(0.82)
120	(248)	3.670	(0.877)	1006.66	(62.84)	0.4168	(0.2408)	0.5252	(0.53)

### **Product Stewardship**

The Dow Chemical Company and its subsidiaries ("Dow") has a fundamental concern for all who make, distribute, and use its products, and for the environment in which we live. This concern is the basis for our Product Stewardship philosophy by which we assess the safety, health, and environmental information on our products and then take appropriate steps to protect employee and public health and our environment. The success of our Product Stewardship program rests with each and every individual involved with Dow products—from the initial concept and research, to manufacture, use, sale, disposal, and recycle of each product.

### **Safety Considerations**

Material Safety Data (MSD) sheets are available from The Dow Chemical Company. MSD sheets are provided to help customers satisfy their own handling, safety and disposal needs and those that may be required by locally applicable health and safety regulations. MSD sheets are updated regularly, therefore, please request and review the most current MSD sheet before handling or using any product. These are available from the nearest Dow sales office.

### **Customer Notice**

Dow encourages its customers to review their application of Dow products from the standpoint of human health and environmental quality. To help ensure that Dow products are not used in ways for which they were not intended or tested, Dow personnel will assist customers in dealing with ecological and products safety. Your Dow sales representative can arrange the proper contacts.

#### Contact information:

For more information about this product please call The Dow Chemical Company.

North America: 1-800-447-4369 Latin America: (+55) 11-5184-8722 Europe: (+31) 11-567-2626 Asia/Pacific: (+60) 3-7965-5392 http://www.dowtherm.com NOTICE: No freedom from infringement of any patent owned by Dow or others is to be inferred. Because use conditions and applicable laws may differ from one location to another and may change with time, Customer is responsible for determining whether products and the information in this document are appropriate for Customer's use and for ensuring that Customer's workplace and disposal practices are in compliance with applicable laws and other government enactments. The product shown in this literature may not be available for sale and/or available in all geographies where Dow is represented. The claims made may not have been approved for use in all countries. Dow assumes no obligation or liability for the information in this document. References to "Dow" or the "Company" mean the Dow legal entity selling the products to Customer unless otherwise expressly noted. NO WARRANTIES ARE GIVEN; ALL IMPLIED WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE ARE EXPRESSLY EXCLUDED.

