




STANDARD CEMENT

A.MIG-2044

Quick Tips



1. The Standard Cement (A.MIG-2044) shown here is formulated to have an intermediate density between Extra Thin Cement (A.MIG-2025) and Medium Dense Cement (A.MIG-2038).

Por último, vamos a ver el Standard Cement (A.MIG-2044). Está formulado para tener un densidad intermedia entre el Extra Thin Cement (A.MIG-2025) y el Medium Dense Cement (A.MIG-2038).



2. It is perfect for use in medium sized parts that require a small margin of time to be placed. This cement is ideal for precision application without overflow marring the neighbouring surfaces.

Es perfecto para usarlo en piezas de tamaño medio que requieran un pequeño margen de tiempo para situarlas. Permite aplicarlo con precisión sin que llegue a desbordar por los laterales evitando manchar la pieza.



3. To achieve a firm bond, it is sufficient to keep the parts pressed for a few seconds. The bond will be cured completely in 15 min.

Para conseguir una unión firme, es suficiente mantener las piezas presionadas durante unos segundos. Secará por completo en 15 min.

4. In this image you can see the differences in the finish with each of the three glues.

En esta imagen podemos ver las diferencias en el acabado de los tres pegamentos.

