

# STERO SD1 DOOR-TYPE DISHWASHER







#### STANDARD FEATURES

- 1.7 gallons per rack
- 37 racks per hour
- Stainless steel construction
- Field adjustable from straight to corner operation
- Door cycle switch controls machine operation
- Filling machine initially, auto fill after first cycle, fill time field adjustable
- Solenoid operated positive seating drain valve open and closed, no water waste
- Chemical pumps included
- Interchangeable upper and lower wash arms
- 1 H.P. pump motor
- Self-flushing stainless steel pump strainer, large scrap accumulator

	SD1	
MACHINE RATINGS	Chemical Sanitizing	
Racks per Hour (Maximum)	37	
Wash Motor H.P.	1	
Rinse Cycle – Gallons per Rack	1.7 Gallon/Rack	
Incoming Water Temperature ( Recommended Minimum)	140°F	
Required Minimum Final Rinse Temperature	120°F	

МО	ELECTRICAL CONNECTION MOTORS AND ELECTRIC TANK HEAT			
ELECTRIC SPECS.	RATED AMPS	MINIMUM SUPPLY CIRCUIT CONDUCTOR AMPACITY	MAXIMUM OVERCURRENT PROTECTIVE DEVICE	
120/60/1	14.0	20	20	

MACHINE WEIGHT			
MODEL	NET WEIGHT	SHIPPING WEIGHT	
SD1	210 lbs.	235 lbs.	

OVERALL DIMENSIONS: 69"H x 29"W x 32-1/2"D

ST50402 (11/14) Page 1 of 2

## **STERO SD1**

### **DOOR-TYPE DISHWASHER**



**PLUMBING NOTES:** 

**MISCELLANEOUS NOTES:** 

WATER HAMMER ARRESTOR (MEETING ASSE-1010 STANDARD OR EQUIVALENT) TO BE SUPPLIED


(BY OTHERS) IN COMMON WATER SUPPLY LINE AT SERVICE CONNECTION. RECOMMENDED WATER

HARDNESS TO BE 3 GRAINS OR LESS FOR BEST RESULTS.

### **A** WARNING

Electrical and grounding connections must comply with the applicable portions of the National Electrical Code and/or other local electrical codes.

Plumbing connections must comply with applicable sanitary, safety and plumbing codes. Drain and fill line configurations vary, some methods are shown on this drawing.



PREVENT LEAKAGE In line with its policy to continually improve its products, Stero reserves the right to change materials and specifications without notice.

21-3/4"