
# Now faster and more predictable!



# Reliable, tight contacts

Drawn-wire nickel titanium plus PEEK produces consistent separating pressure longer!

# predictable contours

Marginal ridge enhancements built into the matrix bands AND rings help provide that finishina flair!

# Easier, more

The Strata-G<sup>™</sup> rings, bands and wedges combine for a 270° Seal<sup>™</sup> for ultimate flash control. The rings won't spring off the tooth, and the amazing Wide Preparation ring makes tough wide preps no problem.

Faster, less frustrating

Class IIs

Strata-G<sup>™</sup> forms a 270° Seal<sup>™</sup> for ultimate flash control.

# the all new





# Strata-G<sup>™</sup> Sectional Matrix System:



- + Operator-friendly retaining system
- + Naturally contoured bands
- + Anatomically correct contacts
- + Contacts at the height of contour
- Rings produce optimal tooth separation for excellent, tight contacts

**Garrison** contactme@garrisondental.com www.garrisondental.com | www.stratagmatrix.com the all new

# RATA-ET RATA-ET RATA-ET





the all new








**Garrison** 

# **270° Seal**<sup>™</sup> for ultimate flash control!



# Longer lasting by design.

Advanced materials and design combine to produce our longest lasting, most predictable separator ring ever!

## Strong tooth separation yet easier to open!

Nitinol drawn-wire nickel titanium is aligned at the molecular level for superior performance yet requires less effort to open. Garrison's proprietary StrataSet™ treatment maximizes the longevity of this advanced material.

#### More uses!

The PEEK ultra-durable reinforcement on the back of the ring allows Strata-G™ to retain a higher percentage of initial strength for much longer than non-reinforced rings. Proprietary StrataBond™ silicone/PEEK tips withstand hundreds of applications.

# Improved anatomy-Unbeatable grip



Enhanced marginal ridge guides and supports matrix bands.

StrataBond<sup>™</sup> silicone for unsurpassed flash control.

Ultra-Grip™ retention extensions provide tenacious grip and are gentler to the papilla.



Short blue ring refill



Tall orange ring refill (qty 2)



Wide prep green ring refill (qty 2)

**SGR01** Three ring kit (1 per color)

# Flexibility for a better cervical seal!

Stack them up

No back-out

Strata-G<sup>™</sup> Wedges utilize Soft-Face<sup>™</sup> materials and

The smooth tunnel design easily accommodates

wedging from the buccal and lingual is desired.

Soft retentive fins smoothly fold down

during wedge insertion and spring back

when clear of the interproximal space,

The inverted V shape sits lower and seals deeper

interproximally while flexible side walls and Soft-

locking Strata-G<sup>™</sup> Wedges in place.

A better seal by design

stacking of wedges. This feature is extremely helpful in cases of gingival recession or when simultaneous

advanced design to promote a better fit.







### Wider indicationswider smiles!

Dentistry's premier Wide Preparation separator ring (green) makes Strata-G<sup>™</sup> the most versatile and user-friendly system available. Tackle the most challenging posterior restorations with confidence knowing that you will achieve excellent contact and contour.



# Face<sup>™</sup> TPE over-mold allow Strata-G<sup>™</sup> Wedges to easily adapt to concavities and irregularities.

SGK4-M

STRATA-G ™

Wedge Kit

gty 200



# 

ensure you have the best matrix band to restore every case. Optimized marginal ridge

Strata-G<sup>™</sup> Bands provide shape and quidance for developing the marginal ridge of Class II restorations without blocking your access.

Anatomy top to bottom

Five sizes of super-thin stainless steel in both dead-soft and firm



## ProfileBooster<sup>™</sup> subgingival apron

Achieving a natural emergence profile in challenging cervical areas is easy with Strata-G<sup>™</sup> Bands–it's built right in!













 Non-stick and color coded • Easy placement tabs

# Firm Bands for challenging cases

A critical addition in the Strata-G<sup>™</sup> kit, Firm Bands are specially tempered stainless steel and only 0.0015" thin. Their stiffer nature makes them ideal for unbroken contacts and extra deep or extra wide preparations.



STRATA-G™ assorted bands kit

> in 5 sizes aty 200





faster-more predictable-flash control



www.stratagmatrix.com

Assorted firm band minikit