

# Pocket Digital Thermometer Model 314 3058302

*To measure temperature with this unit, follow these simple instructions:*

Select either the Fahrenheit or Celsius mode:

● With the unit 'OFF' press and continue to hold the ON/OFF button. The LCD will alternate between °F and °C.

● Release the ON/OFF button when desired measurement mode appears on the LCD.

Remove the protective sheath from the stem.

Press the ON/OFF button.

Insert stem into area or object to be tested. At least 1/2" of the stem must be inserted.

**Warning:** The stem is a sharp and pointed object which can be dangerous.

The Data Hold function is used by pressing the D-H button when taking a measurement. The Measurement will flash on the LCD when Data Hold is in use. To return to normal function, press and release the D-H button a second time.

Press the ON/OFF button to end operation, or the unit will automatically power off after 35 minutes.



## Specifications:

Range..... -58° to 300°F / -50° to 150°C

Resolution..... 0.1°F/C

Accuracy..... ±2°F, ±1°C

Sampling Time..... 1.5 seconds

Battery..... 1.5 Volt Button

(Part No. AB13; SR44)

**THIS INSTRUMENT** is in compliance with  
EN 50 081-1:1992, EN 50 082-1:1992,  
IEC 801-2:1984, IEC 801-3:1984, IEC 801-4:1988



**COMARK**

A Fluke Company

Comark Instruments

Tel: (503) 643 5204

Fax: (503) 644 5859

Email: sales@comarkUSA.com

www.comarkUSA.com

Made in Korea