

●● sueno pro S



- Tinnitus-Module
- 9 Channels
- Up to 4 Programs
- Rocker Switch (programmable)
- Low Battery Indicator
- Start-up Delay
- Data Logging
- nanoShield


**Equipment:**

- Thin Tube System

**Technical Data**

**EN 60118-0:2015** (2 cm<sup>3</sup>-coupler) & **ANSI S3.22-2014** (2 cm<sup>3</sup>-coupler)

Operating Voltage	1,30 V
Noise Level (RMS)	69 dB
Frequency Range	100 Hz–8000 Hz
Battery Current	1,18 mA
Battery Type	312
Average Battery Life (Zinc-Air)	120 h



- 1 Rocker switch
- 2 Battery compartment/  
On-Off-switch
- 3 Battery compartment lock

**Standard**



**Programming**

Cable:	Cabel Set H or I
Battery:	without Battery
Progr.-Box:	HI-PRO/HI-PRO 2 HI-PRO USB NOAHlink
Software:	audifit 5.8



●● sueno pro S

All curves are measured with 2 cm<sup>3</sup>-coupler (EN 60318-5:2015) in reference setting.

