

ProMegJig™

metal, easy, grip

LARGE

PRODUCT SPECIFICATION

46/PROMEGJIG-L
46/PROMEGJIG-LG
46/PROMEGJIG-LC
46/PROMEGJIG-LPB

Chrome
Gold
Copper
P/Black



Scan QR code to see video demonstration




Features & Benefits

- World's first Flat Pour™ jigger
- Available in World, US & CAN versions
- Dual 30/60 mL or 1 Oz/2 Oz measures
- Trilobal shape reduces or eliminates surface lens (meniscus)
- Angled jigger head provides clean directed pour streams
- Pour edges eliminates loss transference from hand shake

*Meniscus adds approx. 3-5 mL (0.1 Oz - 0.16 Oz) of alcohol

| SPECIFICATIONS | | | | |
|------------------|------------------|------------------|------------------|------------------|
| Item Number | 46/PROMEGJIG-L | 46/PROMEGJIG-LG | 46/PROMEGJIG-LC | 46/PROMEGJIG-LPB |
| Volume Size | | | | |
| VOL1 | 1 Oz (30 mL) | 1 Oz (30 mL) | 1 Oz (30 mL) | 1 Oz (30 mL) |
| VOL2 | 2 Oz (60 mL) | 2 Oz (60 mL) | 2 Oz (60 mL) | 2 Oz (60 mL) |
| Dimensions | | | | |
| A - Length | 101 mm (3.9 in) | 101 mm (3.9 in) | 101 mm (3.9) | 101 mm (3.9) |
| B - Width | 55 mm (2.2 in) | 55 mm (2.2in) | 55 mm (2.2in) | 55 mm (2.2in) |
| Weight | 93grms (0.2 lbs) | 93grms (0.2 lbs) | 93grms (0.2 lbs) | |
| Construction | Stainless-steel | | | |
| Custom Logo Area | | | | |
| E - Length | 25 mm (0.98 in) | | | |
| Decoration | Laser Engraved | | | |
| Technique | | | | |



Des.Reg.Pat.

ProMegJig™

metal, easy, grip

LARGE

PRODUCT CARE GUIDE

ProMegJig™L Compartments

1

Usage, Washing & Caring

2

Using the ProFlow™ speed pourer, pour liquid into the ProMegJig™L until it touches the brim

Pour from the ProMegJig™L into Boston tin/glass

The ProMegJig™L can be cleaned in warm/soapy water

Alternatively the ProMegJig™L can be cleaned in soda water

WARNING
NEVER CLEAN WITH ABRASIVE MATERIAL OR HARSH CLEANING CHEMICALS/SOLVENTS
THOROUGHLY DRY AFTER CLEANING

WARNING
NEVER PLACE ANY PART INTO A GLASS WASHER, DISH WASHER OR BOILING WATER