
























More information on the website
radwag.com/en/info,w1,K2M

MYA 11.5Y Microbalance



Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	11 g
Minimum load	0,1 mg

Metrological parameters	
Readability [d]	1 µg
Verification scale interval [e]	1 mg
Tare range	-11 g
Standard repeatability [5% Max]	0,45 µg
Standard repeatability [Max]	2,5 µg
Standard minimum weight (USP)	0,9 mg
Standard minimum weight (U=1%, k=2)	0,09 mg
Permissible repeatability [5% Max]	1,6 µg
Permissible repeatability [Max]	3,5 µg
Linearity	±6 µg
Eccentric load deviation	6 µg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	max 10 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatic - Reflex Level System
Display	10" touchscreen
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	655×755×445 mm
Net weight	9,1 kg
Gross weight	16,6 kg
Communication interface	
Communication interface	USB-A x2, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,4A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3°C/1h (±1°C/8h)
Relative humidity	40% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Antivibration Tables
Barcode scanners

Weighing dishes
Fingerprint Reader

Professional weighing table
USB Hubs
THBR 2.0 System - Ambient Conditions Monitoring

RS 232 – USB Converter
RS 232, RS 485 cables

Software

RAD-KEY
LabVIEW Driver
RADWAG Remote Desktop
Scales Editor 2.1
R.Barcode

Audit Trail Reader
Label Editor R02
R-LAB
RADWAG Development Studio

Device dimensions

