

— EVERY JOURNEY TELLS A STORY.

LOGISTICS MASTER™



Logistics Master™ is the **premiere quality control tool** for shipping live and frozen food products.

At the touch of button, record the entire journey and **gain key insight** into the two leading causes of food mortality and lost revenue - temperature and motion.

Built for the long haul

Featuring a waterproof design, records data of the entire journey*, regardless of environment or shipping disruptions.

Data led quality control

Leverage tracking information with Logistics Master™ data. Gain customer loyalty with a data-led shipping quality and transparency.

*up to 7 days



Approx. actual size

Triple sensor data collection

Measure **Internal temperature**, **External temperature** and **Vibration**. Pinpoint **when**, **where**, and **why** product damage occurred.

Stress-free activation

Start recording at the touch of a button.

Logistics Master™ delivers the quantifiable quality assurance you need to secure **customer confidence** and **loyalty**.



Logistics Master™ 4G specifications


Model Number	LM4GV01
Device Size	114.5x71.5x22 mm / 4.51x2.81x0.87 in.
Device Size with Packaging	N/A
Cable Length	117 cm
Weight	145 g / 0.32 lb
Battery	2,000 mAh Rechargeable Lithium Battery
Recording (Power On)	Up to 7 days
Standby Time (Power Off)	Up to 1 year
Operation Temperature	-20~50 °C
IP Rating	IP66
Persistent Recording	Yes
Data Display Interval	120 seconds (Highest recorded value)
Data Entries	Up to 20,000 entries
Acceleration Sensor	Digital 3-axis Accelerometer
Measurement Range	±8 g-force (±0.05 g-force)
Sensitivity Range	0.001 g-force
Temperature Sensor	Dual Digital Temperature Sensors
Measurement Range (Internal)	-20~65 °C (±0.5 °C)
Measurement Range (Ambient)	-40~105 °C (±0.5 °C)
Sensitivity Range	0.5 °C

📶 Low investment, high return


Collect days worth of data with almost ZERO impact to your shipping weight.

☁️ Touchless Data Upload

Get all the data without lifting a finger after activation.



How to use:



Stick the device to the outside of the product crate.

Press button to activate the device (cannot be deactivated).



NB Office: Annex 1 - 40 Charlotte Street, Saint John, New Brunswick, Canada E2L 4V1
 NS Office: Unit 100 - 1505 Barrington Street, Halifax, Nova Scotia, Canada B3J 3K5
info@marinethinking.com
sps.marinethinking.com

