

EC LIPSE™ GEN2



FEATURES & SPECIFICATIONS

General Description

The Eclipse™ Gen2 is ideal for vertical farm applications, but is also suitable for a wide range of other horticulture applications including: greenhouses, growth chambers and tissue culture laboratories. The Eclipse Gen2 single bar is designed to deliver high levels of photosynthetic photon flux (PPF) values with unsurpassed light uniformity, all within a slim and water-proof design. For easy installation, the Eclipse Gen2 fixtures can be daisy-chained together in runs of up to 15 fixtures (22 for low wattage option). Fixtures are supplied with spring clips for surface mount or unistrut installations.

Mechanical Construction

Single, 46-inch anodized aluminum extrusions provide thermal management and housing for drivers and wiring. High temperature, molded-silicone gaskets and injection-molded polymer end caps provide IP66-rated ingress protection from dust and moisture. 5-conductor cables and water-tight, locking connectors provide power and dimming from bar to bar. Each bar includes pigtail and male connector on one end and a female connector on opposite end. Maximum bar to bar spacing is 18 inches on centers.

Electrical Specifications

Each Eclipse Gen2 fixtures includes an internal dimmable driver. Input voltage is 120-277VAc and 50-60Hz. 0-10V dimming is standard.

LEDs

The 50° beam angle utilizes Illumitex's patented Digital Distribution technology ensuring that the maximum light intensity is delivered directly to the crop canopy at higher mounting heights (12 to 36 inches).

Weight

5.4 lbs

Finish

Clear anodized extrusions with black molded gaskets and end caps.

Power Consumption

65 watts for 12 LED's in F3 spectrum (consult factory for wattage of other spectrums, 80 Watts max)

Testing & Compliance

IP66 ingress protection rating

RoHS compliant

ETL/cETL listing for damp location

CE Marking


5-year warranty

50,000 hour life



STANDARD SPECTRA

F3 SPECTRUM



BEST FOR GERMINATION THROUGH FLOWERING

The F3 spectrum is the workhorse and most popular spectrum from Illumitex. It produces the fastest germination and drives the best vegetative and flowering results among all of the spectra options. In addition to the blue and red wavelengths, the F3 spectrum contains a small amount of green which is beneficial for the quality assessment of plants. The F3 spectrum is recommended for use in growth chambers as well as controlled environment agriculture operations of any size.

F3 WAVELENGTH MIX

Blue (400 - 499 nm)	22.4 ± 1.3%
Green (500 - 599 nm)	13.4 ± 0.6%
Red (600 - 699 nm)	63.9 ± 0.8%
Far Red (700 - 780 nm)	0.4 ± 0.1%


FIXTURE EFFICIENCY

SPECTRUM	FIXTURE PPF	FIXTURE WATTAGE	μmol/J
F3	104	65	1.6

illumitex[®]

EC LIPSE[™] GEN2

F1 SPECTRUM




F1 WAVELENGTH MIX

Blue (400 - 499nm)	22.8%
Green (500 - 599nm)	0.3%
Red (600 - 699nm)	76.8%
Far Red (700 - 780nm)	0.1%

GENERAL PURPOSE, HIGH EFFICIENCY

F1 spectrum is suitable throughout the plant growth cycle and offers the highest photon yield efficacy of the available spectra. F1 is recommended for applications with a tight energy budget where visual plant assessment is not a priority.

X5 SPECTRUM




X5 WAVELENGTH MIX

Blue (400 - 499nm)	18.0%
Green (500 - 599nm)	17.0%
Red (600 - 699nm)	64.0%
Far Red (700 - 780nm)	0.0%

BEST FOR HUMAN VISUALIZATION

Inspired by the work of NASA scientists, X5 spectrum delivers the highest level of light within the green band of the PAR spectral range, thus providing the best spectrum option for plant quality assessment.

F6 SPECTRUM




F6 WAVELENGTH MIX

Blue (400 - 499nm)	49.5%
Green (500 - 599nm)	0.5%
Red (600 - 699nm)	49.9%
Far Red (700 - 780nm)	0.1%

BEST FOR VEGETATIVE GROWTH

F6 spectrum provides an enhancement in the 400 to 499nm region ensuring the fastest vegetative growth results. The increased blue content reduces overall plant height and improves plant appearance and space utilization.

F7 SPECTRUM



F7 WAVELENGTH MIX


Blue (400 - 499nm)	74.5%
Green (500 - 599nm)	0.6%
Red (600 - 699nm)	24.8%
Far Red (700 - 780nm)	0.1%

BEST FOR SEEDLINGS

F7 spectrum delivers the highest blue content of all available spectra. This spectra produces stocky plants with the shortest internodal distances which is highly desirable at the seedling stage of growth.


SUPPLEMENTAL LIGHTING

450nm BLUE WAVELENGTH




The 450nm wavelength is recommended as supplemental light for seedlings and young plants during the vegetative stage of their growth cycle, especially when “stretching” must be reduced or eliminated.

525nm GREEN WAVELENGTH




The 525nm wavelength LED can be used as a tool for eliciting specific plant responses such as stomatal control, phototropism, photomorphogenic growth and environmental signaling.

624nm RED WAVELENGTH




This 624nm region has the highest photosynthetic relative quantum yield for a range of plants. Its action on red-absorbing phytochrome is considerably weaker compared to that of 660nm red light.

660nm DEEP RED WAVELENGTH



The 660nm wavelength exhibits the highest action on red-absorbing phytochrome regulated germination, flowering and other processes. Most effective for light cycle extension or night interruption to induce flowering of long-day plants or prevent flowering of short-day plants.

730nm FAR RED



Although the 730nm wavelength is outside the photosynthetically active range, but it has the strongest action on the far-red absorbing form of phytochrome and can be used at the end of each light cycle to promote flowering in short-day plants.

FIXTURE PPF VALUES

SPECTRUM	F1	F3	X5	F6	F7
TYPICAL PPF	108	104	102	103	87

* 50° beam; 12 LEDs

EC LIPSE™ GEN2

PART NUMBER ORDERING GUIDE

ESN	1	48			U	D
SERIES	# OF BARS	BAR LENGTH	# OF LEDs	LED SPECTRA	INPUT	DIMMING
ESN = 50° beam	1 = Single Bar	48 = 48" Over all length	12 = 12 per Bar 08 = 8 per Bar for low-wattage	Growth: F1 = F1 F3 = F3 X5 = X5 F6 = F6 F7 = F7 Supplemental: 45 = 450nm 52 = 525nm 62 = 624nm 66 = 660nm 73 = 730nm	U = 120-277Vac	D = 0-10V Dimmable (standard)

* Optional 10-foot cable extension accessory CE5-10. Ordered separately.
** 6-LED option only applies to 50° beam

INPUT SPECIFICATION


Parameter	Min.	Typ.	Max.	Notes
Input Voltage	120 Vac		277 Vac	
Input Frequency	50 Hz		60 Hz	
Input AC Current *See NOTE 1		0.57		Measure with F3 spectrum at 120 Vac
Power Factor		0.99		120 Vac, Full load
Power		65W		Measured with F3 spectrum at 120 Vac

Notes:

1. Input power varies per spectrum

DIMMING FUNCTION

Io/Ioset vs. Dimming voltage



Notes:

1. The maximum current draw of the dimming input (DIM+) is 0.15mA. This will determine the total number of dimming wires that can be tied together to one controller.

ACCESSORIES (order separately)

CE5-10CH1 (Cable extension, 5-conductor, 10-foot, female connector + flying leads) = power input @ first bar (see wiring diagram)

Wiring Diagram for CE5-10CH1 Input Cable

Black Wire	Line
White Wire	Neutral
Green Wire	Ground
Red Wire	Dimming +
Orange Wire	Dimming -


CE5-10CH2 (Cable extension, 5-conductor, 10-foot, female connector + male connector) = bar to bar extension

CONTROLS (order separately)

WS-JBOX-ESG2: Wireless node j-box

WS-Node-IP: Wireless node, single-phase 120-277Vac

WS-225C: Wireless Gateway



EC LIPSE™ GEN2

DIMENSION LINE DRAWINGS

