






RoHS 2011/65/EU & (EU) 2015/863 COMPLIANT

REV.	DESCRIPTION	DATE
△		2023/01/05
△	ITEM5 changed to English and French warning labels	2023/02/06

CUSTOMER: P/N: MD204-06 REV. APPROVED BY:

△ ⑤ Hosp. Grade label





ITEM	DESCRIPTION	QTY	COLOR
⑩	Cable ties	1	WHITE
⑨	LABEL 4	1	---
⑧	LABEL 3	1	---
⑦	LABEL 2	1	---
⑥	LABEL 1	1	---
⑤	Hosp. Grade label	1	WHITE
④	Plastic cap	1	RAL 9016 (WE-2985)
③	SJTW 14AWG 3C 105°C	1	APPROVAL: UL,CUL
②	WS-161-11A(5-15R)	1	APPROVAL: UL,RU
①	WS-001H(5-15P)	1	APPROVAL: UL,CUL

ITEM	DESCRIPTION	QTY	COLOR
⑩	Cable ties	1	WHITE
⑨	LABEL 4	1	---
⑧	LABEL 3	1	---
⑦	LABEL 2	1	---
⑥	LABEL 1	1	---
⑤	Hosp. Grade label	1	WHITE
④	Plastic cap	1	RAL 9016 (WE-2985)
③	SJTW 14AWG 3C 105°C	1	APPROVAL: UL,CUL
②	WS-161-11A(5-15R)	1	APPROVAL: UL,RU
①	WS-001H(5-15P)	1	APPROVAL: UL,CUL

NOTES:

- Each PCS is first wrapped with bubble cloth, then packed in a small bag, and has a built-in instruction manual.
- "HOSPITAL GRADE" is bold.
- Please refer to 0096-1729-1 Rev.B.
- The baking point of the iron shell cannot fall off.
- The breaker should be assembled in place.
- WS-161-12A needs to refer to CNS when feeding the upper and lower covers Standard salt spray test.
- Medical-grade sockets use anti-foreign object sockets (socket apply tamper resistance)
- LABEL 4 is attached to the edge of WS-161-11A.
- LABEL 2 and 3 are attached to the bottom of the box.
- Please note that this product does not have LED lights.
- Changhua production started to issue "E version" ZH(Zhang Hua) factory begin from revision E
- The outer box must be marked with RoHS (RoHS shown on the carton)
- Lock socket without gasket (No fiber washer on the screws holding the duplex outlets)
- The lock socket uses S-head screws (Use S type self locking screw to lock outlets)
- On the screw teeth at the bottom of the S head dip the screw fixative (material number: BB-2100) on the lock, and let stand for 24 hours.
- Moistens the screw fixing agent (S base spiral tooth place, BB-2100) is locking, and settles for 24 hours. (the material number: BB-2100) is locking, and settles for 24 hours.
- Refer to the content and specifications of LABEL 2 and 3: 0096-1729-2, Rev.A



頭	尾	線種	線規	芯線數	溫度	顏色	總長度
WS-001H-1	WS-161-11A	SJTW	14AWG	3C	105°C	WE-2985	1830mm



AC Connectors of Cordtec Power Corp
 Main: 1-414-434-2220 Fax: 1-414-323-8386 Text: 1-414-323-3240
 Email: Info@CordtecPower.com

Website: CordtecPower.com/ ACWORKS.com