

DERMASTIR Wrinkle Filler - 30ml

DERMASTIR Wrinkle Filler has been developed and produced by Alta Care Laboratoires as an instant anti-wrinkle filler. DERMASTIR Wrinkle Filler is unique in its genre since it combines two immediate actions: filling and myorelaxant, which means that the cream fills in wrinkles and, at the same time, relaxes and smoothes out both superficial and deep facial wrinkles. DERMASTIR Wrinkle Filler has a rich texture and leaves a pleasant silky sensation on the skin after the application.

The use of DERMASTIR Wrinkle Filler is recommended after plastic surgery or other invasive treatments, as its muscle relaxant action is safe and there is no risk of side effects.



POST PLASTIC SURGERY



POST BOTOX FILLER



POST LASER



POST BIOREVITALIZATION



ANTI WRINKLE



DERMASTIR WRINKLE FILLER

SODIUM HYALURONATE	<input type="radio"/>
COLLAGEN	<input type="radio"/>
ADENOSINE	<input type="radio"/>
LECITHIN	<input type="radio"/>
PALMITOYL PENTAPEPTIDE-4	<input type="radio"/>
PHYTOEXTRACTS	<input type="radio"/>

Directions For Use

Apply the Wrinkle Filler both during the day and in the evening directly on the wrinkles. Helps to improve the condition of the skin, helping to deal with the signs of the aging and dry skin.

DERMASTIR®

WWW.DERMASTIR.COM



WRINKLE FILLER

LABORATOIRES

ALTA
CARE


6, Piazza di Spagna - 00187 Roma, Italia.
www.altacare.com

MADE IN FRANCE

Dermastir Wrinkle Filler - 30ml

Dermastir Wrinkle Filler acts on all types of wrinkles, including expression and forehead wrinkles. Dermastir Wrinkle Filler helps to reduce the appearance of skin blemishes such as scars, stretchmarks and large pores, since the volume of dermal matrix increases. The skin appears more youthful, lifted and regenerated.

All the ingredients are protected in the airless vacuum jar.



**AIRLESS
PUMP TECHNOLOGY**
Protects from oxidation

**Metallic Reflecting
Technology**
Protects from infrared
rays and radiant heat

**Actuator Airless
Technology**
Protects from
bacteria

**Vacuum Flask
Technology**
Protects from
conductive heat

Oxygen
Airless jar protects from oxidation. The ingredients maintain their bioavailability from the first till the last application.

Heat
Thermos effect. The airless packaging consists of 3 jars nested into 1, protecting from conductive heat.

Light
Metallic coating reflects infrared rays, protecting from the light and direct sun exposure.

Humidity
The airless jar maintains its microclimate and pH level, protecting from the humidity.

Bacteria
Prevents the risk of microbiological contamination. The optimal amount is delivered with the pump. No need to touch the product.

