

Direct Bury Twist-On with Strain Relief



Installation Instructions

IMPORTANT: Turn off power before installing or removing connector. Product to be used in accordance with local and national codes.

- 1. Strip wires 5/8" (15.9 mm).
- 2. Align any frayed strands or conductors.
- 3. Place stripped wires together with ends of insulation even.
- 4. Push conductors firmly into connector and twist onto wire until tight. Wipe sealant in and around conductors and connector opening while tightening. Do not over torque.
- 5. Position conductors as shown in Figure A and close lid. Note: When installing 2 - #18 conductors, position to exit out same side. See Figure B.
- 6. Do not reuse.






Figure A






ISTED.

ALED WIRE CONNECTOR SYSTEM 9L57

Measurements (Inches):

A - 2.28



* UL 486D Listed as a sealed wire connector system. For use in damp, wet, raintight, direct bury and submersible locations. Not to be used in continuous submersion applications.

Selected 600V Wire Combinations

2 #18	1 - 3 #10	1 #14 w/3 - 4 #18
1 - 4 #12	2 #14 w/2 - 4 #16	1 #12 w/2 - 4 #18
3 #14 w/1 - 2 #16, #18, #20 or #22	1 #8 w/1 - 2 #16, #18, #20 or #22	2 #12 w/1 - 2 #14, #16 or #18
4 - 6 #16	5 #14 w/1 #18	2 - 5 #14
1 #8 w/1 #12	1 #12 w/1 - 4 #14 or #16	3 #10 w/1 #18
1 #10 w/1 - 5 #16	3 #12 w/1 #14	1 #10 w/1 - 3 #14

Contact factory for a complete list of wire combinations at 800.633.0232.

50100-52 REV F 11/17

U.S. Pat. 7,170,005, 6,815,616, 7,122,742 and Additional Patents Pending apply. All other trademarks, U.S. & Foreign Patents Pending apply. All Rights Reserved.





www.kinginnovation.com (P) 800.633.0232 (F) 636.519.5410

DryConn[®] DBSR[®] Black Medium

Catalog #	Selling Unit
63415	Canister of 15
63475	Box of 100

PRODUCT SPECIFICATIONS & MEASUREMENTS

Max. Voltage: 600V Connector Size: 1.75" x 2.28" Wire Type: Copper/Copper Wire Range: Min #22/Max #6 Silicone Sealant: -45°F to 400°F **UL** Designation: MSR

B - 1.05

No additional wire connector needed.

Integrated twist-on connector.

Strain Relief Lid