

THERMOPLASTIC PRESSURE REGULATORS

Designed for Higher Flow Capacities
with Less System Pressure Loss

SUPERIOR FEATURES:

- Converts varying inlet pressure up to 150 PSI, to a stabilized, lower preset downstream pressure.
- Protects sensitive downstream tools, instruments, tubing and filters against damage from overpressure/pressure surges; permits the entire system to operate safely and effectively.
- Downstream pressure settings adjustable from 5 to 125 PSI.
- Large surface area of its frictionless rolling diaphragm provides exceptional sensitivity.
- Free movement of the diaphragm on a balanced shaft assures smooth, accurate performance and reliable sealing for millions of cycles.
- Double U-cups prevent leakage along the shaft and eliminates the possibility of "creep".
- Optional gauge ports to assist with setting and monitoring pressure.
- For corrosive and ultra-pure liquid applications.
- PVC and CPVC models certified to NSF/ANSI 61 and NSF/ANSI 372.

MATERIALS OF CONSTRUCTION AND PIPING CONNECTIONS:

Bodies available in Geon PVC, Corzan CPVC, Natural Polypropylene, Kynar PVDF. Some Kynar PVDF components are used in the Natural Polypro models for strength. Seals are FKM (Viton) or EPDM. Custom materials available. Connections in NPT, socket, spigot, flange, flare, sanitary. BSP, JIS and DIN connections available.



OPERATION:

Pressure regulators prevent downstream pressure from exceeding the desired set pressure. Regulator will remain closed as long as set pressure is maintained. As equipment or valves downstream of regulator begin to open and demand flow, the downstream pressure begins to fall and the regulator begins to open. As valves or equipment downstream open further, the pressure regulator continues to open until the maximum

opening is reached. As the process is reversed, downstream pressure begins to increase and the regulator starts closing. When the downstream pressure again reaches set pressure the regulator closes bubble-tight. **IMPORTANT:** A pressure regulator does not maintain a specific downstream pressure, but only prevents the downstream pressure from exceeding a set point.

JJD

JJ DOWNS INDUSTRIAL PLASTICS INC.



416.236.1884

Toronto, ON

JJDOWNS.COM

PRESSURE REGULATOR SELECTION:

In the selection of a liquid pressure regulator, flow capacity with minimum system pressure loss are critical criteria, but it should be recognized that all similar-size competitive regulators do not provide similar performance levels. These regulators provide not only higher set pressures and flow capacities with each model, but these are achieved with less pressure losses than with similar size competitive regulators. These lower pressure

drop-offs can be seen from the performance curve charts shown on the following pages. Performance curve charts below identify the high flow capacities and the low pressure drop-off of Plast-O-Matic regulators which result in their greater sensitivity, finer adjustability and superior accuracy as compared to competitive models.


PERFORMANCE CURVES:

Flow Capacity vs. Pressure Drop-Off (PSI)



Comparison of Representative Plast-O-Matic Models with Competitors

Drop-off is the difference between the pressure regulator set pressure and the downstream pressure at flow.

1/2" PRESSURE REGULATOR




1/2" Socket or Threaded





1/2" Spigot


3/4" PRESSURE REGULATOR



3/4" Socket or Threaded





3/4" Spigot




1" Socket or Threaded

1" PRESSURE REGULATOR





1" Spigot




1 1/2" Socket or Threaded

1 1/2" PRESSURE REGULATOR





1 1/2" Spigot




2" Socket or Threaded

2" PRESSURE REGULATOR



2" Spigot

The drop-off is the difference between the pressure regulator set pressure and the downstream pressure at flow.



COMPLETE DIMENSIONS & METRIC SIZES

Valve Size			A		B		C		D	
NPT	DIN	JIS	in	mm	in	mm	in	mm	in	mm
1/2"	20	22	3.19	80.96	8.75	222.25	2.13	53.98	4.94	125.41
3/4"	25	26	5.50	139.70	10.12	255	2.38	60.33	8.81	223.84
1"	32	32	5.50	139.70	10.12	255	2.38	60.33	9.06	230.1
1 1/2"	50	48	6.06	153.99	11.94	303.21	3	76.20	10	254.00
2"	63	60	6.56	166.69	11.94	303.21	3	76.2	10.88	276.23

SERIES "PRHM" MODEL NUMBER

Maximum Flow:



Above, the 1/2" body style.

Valve Size			Flow Rates GPM*	Threaded	Sockets	IPS Spigots	Metric Spigots
NPT	DIN	JIS					
1/2"	20	22	10	PRHM050V-PV	PRHM050VS-PV	PRHM050VSP-PV	PRHM20VSP-PV
3/4"	25	26	35	PRHM075V-PV	PRHM075VS-PV	PRHM075VSP-PV	PRHM25VSP-PV
1"	32	32	50	PRHM100V-PV	PRHM100VS-PV	PRHM100VSP-PV	PRHM32VSP-PV
1 1/2"	50	48	70	PRHM150V-PV	PRHM150VS-PV	PRHM150VSP-PV	PRHM50VSP-PV
2"	63	60	100	PRHM200V-PV	PRHM200VS-PV	PRHM200VSP-PV	PRHM63VSP-PV

* Note: The generally accepted safe velocity in plastic piping is five feet (5'/1.5m) per second. These maximum flow rates exceed that velocity.

Part numbers shown are PVC body, FKM (Viton) seals. For EPDM seals, change "V" to "EP", for example, PRHM050EPS-PV. For CPVC body, change suffix "PV" to "CP", for example, PRHM050VS-CP.

For natural polypropylene, use "PP", for Kynar PVDF use "PF".

For optional sanitary connections, change connection code to "SC" **example:** PRHM075VSC-PP.

For flange connections, change connection code to "FL" **example:** PRHM075VFL-PP.

For flare connections, change connection code to "FR" **example:** PRHM075VFR-PP.

For 1/4" and 3" Pressure Regulators, also PTFE Body Regulators, consult catalog PRH.

NOTE: All data for these curves was collected from actual flow tests at Plast-O-Matic Valves, Inc., Cedar Grove, NJ. or manufacturer's published performance data. The measuring equipment used was the same for all regulators tested, and the relative results between different models are considered to be an accurate portrayal of the data.

CAUTION: Avoid quick closing valve downstream of a regulator to eliminate "water hammer" shock that can cause breakage.



PRHM PVC and CPVC body types certified to NSF/ANSI 61 and NSF/ANSI 372

JJD

JJ DOWNS INDUSTRIAL PLASTICS INC.



416.236.1884

Toronto, ON

JJDOWNS.COM