

Courtesy of Stefano's Espresso Care

La Pavoni Europiccola and Professionale Safety Valve Fitting



The ID on the LEFT fitting is approximately 5mm. It is for the OLD Style Stainless Steel sphere, which was eventually replaced by the Teflon mushroom.

Depending on your machine configuration, the correct replacement is either of the following:

- P-39SE - fits models with a double switch(2-position switch), *not* for a green light with red switch or only an On/Off switch)
- P-39SP -fits models with an On/Off switch only, *not* for a 2-position red and white switch or green light with red switch unless you have the smaller ID fitting.

The ID of the RIGHT fitting is approximately 6.5mm and is made for the Brass Plunger/Anti-vacuum Style Valve. The replacement is MP-39SE-SP. This fits machines with an On/Off switch or green light with red switch unless you have the smaller size fitting. The MP-39SE-SP was not used before the late 1990s.

If you cannot accurately measure the ID, pay attention to the rim at the opening as they are clearly different.