



E-FLEX **BLUE**




Blue Heat Treatment provides superior strength while maintaining flexibility to negotiate all canals




• Usage Protocol





	Color	Tip Size	Taper (%)	Taper Indicator	Cross-Section	Length (mm)	Suggested Speed/Torque
E-FLEX BLUE	●	17	8			19	300 rpm, 3 N·cm
	○	15	4			21/25/31	350 rpm 2.5 N·cm
	●	20	4				
	●	25	4				
	●	30	4				
	●	35	4				
	●	40	4				



	Color	Tip Size	Taper (%)	Taper Indicator	Cross-Section	Length (mm)	Suggested Speed/Torque
E-FLEX BLUE	○	15	6			21/25/31	350 rpm 2.5 N-cm
	●	20	6				
	●	25	6				
	●	30	6				
	●	35	6				
	●	40	6				