## ASSEMBLY INSTRUCTIONS

TWO (2) PEOPLE AND PHILIP'S SCREWDRIVER REQUIRED


PLEASE UNPACK ALL PARTS AND CHECK AGAINST PARTS LIST ON THIS INSTRUCTION SHEET BEFORE DISCARDING PACKING AND CARTON!!

- 1) Connect the side rails and headboard / footboard by bolt (F).
- 2) Assemble the side rails and headboard / footboard using the curved washer (A), flat washer (B), lock washer (C), and nut (D) tighten with wrench provided (E), as shown in Diagram A.
- 3) Attach the support legs to slats using flat washer (K), lock washer (L) and bolt (J), tighten with wrench provided (M). Adjust the support leg if necessary as shown in Diagram B.
- 4) Attach the adjustable slats system (H) to the side rails and locked to a needed position, using Philips screw drive to tighten the screw (G) if necessary. Attach the assembled slats & support leg to the adjustable slats system using bolt (N), tighten with wrench provided (R). Using Philips screw drive to tighten the screw (G) if necessary as shown in Diagram C.
- 5) Stick the felt pad on the bottom of metal ferrule.
  - \*\*\* NOTE KEEP THIS SHEET!!! \*\*\*

In the unlikely event that you would need a replacement part for your furniture, please contact your local authorized Schnadig International dealer. If you need replacement hardware quickly, it could be purchased from your local hardware store

	CLA-419-101		CLA-419-121		CLA-419-141	
	QUEEN BED		KG BED		CK BED	
Part Description	Part No.	QTY	Part No.	QTY	Part No.	QTY
Headboard (1)	CLA-419-101-H	1	CLA-419-121-H	1	CLA-419-121-H	1
Footboard (2)	CLA-419-101-F	1	CLA-419-121-F	1	CLA-419-121-F	1
Side rail (3)	CLA-419-101-R	2	CLA-419-101-R	2	CLA-419-141-R	2
Slat (4)	CLA-419-101-F-3067	5	CLA-419-121-F-3067	5	CLA-419-121-F-3067	5
Support leg(5)	CLA-419-101-F-30305	5	CLA-419-121-F-30305	5	CLA-419-121-F-30305	5
RTA Hardware(6)	CLA-419-101-F-3001	2	CLA-419-121-F-3001	2	CLA-419-121-F-3001	2
RTA Hardware(7)	CLA-419-101-R-3001	1	CLA-419-101-R-3001	1	CLA-419-141-R-3001	1
Felt Pad	CLA-419-101-R-30318	6	CLA-419-101-R-30318	6	CLA-419-101-R-30318	6

RTA Hardware (3) For Side rail				
NO.		Q'ty		
Α	1	Curved Washer	8	
В	0	Flat Washer	8	
С	0	Lock Washer	8	
D	9	Nut	8	
Е	M	Wrench	1	
F	/	Bolt	8	
G	<u> </u>	Screw(4.2x20)	20	
Н	વ્ય	Adjustable slats system	10	



RTA Hardware (2) For Support leg						
NO.		Q'ty				
J	() Communication	Bolt	10			
K	0	Flat Washer	10			
L	0	Lock Washer	10			
М	Γ	Wrench	1			
N	•	Bolt	10			
R	_	Wrench	1			
G	<u></u>	Screw(4.2x20)	20			

