BKL2 HydroTap G5 v1.00 02.21 CS Home Ventilation requirements Contact your local service provider if ventilation is not suitable HydroTap Tap options Font options Clearance envelope Elite Plus Classic Plus **Raised Font Font** with 135mm Extension with 135mm Extension **Position the Tap and the Command Centre** as close together as possible. 221 Command Centre 50 width **Tap Positioning** Air outlet louvre (if required) Cut-out in door/wall, towards Ø 108 **Cutting detail Cutting detail** Position the Tap to dispense into the sink, allowing clearance for a cup or teapot. Alternatively, mount the ø35 hole for tap hole for bowl ø86 hole for bowl the top of the cabinet 285 HydroTap Tap on a Font (available as an accessory). for M6 stud \emptyset 35 hole for tap \emptyset 35mm hole for HydroTap Tap Air inlet cut-out (required) Cut-out in cabinet floor 326 \varnothing 10 for M6 stud Sink 116 4mm buffer pad air space Classic Plus Tap Clearance Clearance Envelope **Envelope** Ø**82** CO₂ gas cylinder Mains cold water `Air inlet grille $\,{}^{\setminus}$ IEC Flex & Plug $\,{}^{\wedge}$ isolation valve 230-240V, 50Hz/ (not supplied) power outlet 50 min. 50 min. SCALE 1:5

HydroTap G5 CS Home

Ø **219**

shown with "Classic Plus" Tap