

Front Entry Acrylic Outward Swing Door Walk-In Bathtub Specifications

Actual Size: 32" x 40 x 42 · (81 cm x 102cm x 107 cm)

Seat Width: 24" • (61 cm)

Shipping Size: 34" x 43" x 50" • (86 cm x 109 cm x 127 cm)

Net Weight: 200 lbs. • (91 kg)

Shipping Weight: 280 lbs. · (127 kg)

Unoccupied Water Capacity: 70 gal. • (265 L)

Occupied Water Capacity: 25-55 gal. • (95 - 208 L)

Drainage Time: +/- 140 seconds at ideal plumbing conditions

(unoccupied)

Included Features:

- 1. Acrylic Tub Shell
- · Gloss white finish
- · Fiberglass gelcoat reinforced
- 2. Stainless steel frame with adjustable leveling Legs.
- 3. Outward swinging custom crafted industrial plastic composite door with tempered glass.
- 4. Two (2) access panels.
- 5. One (1) 2 inch PVC drains T-type, two (2) outlet drains with end caps, one (1) overflow and a stainless steel cable operated opener with extended handle in chrome finish.

Jetting & Therapy Options:

- 1. Air + Hydro (Multicolor LED Light Included)
- 2. Hydro Massage (Multicolor LED Light Not Included)
- 3. Hydro Massage + Microbubble (Multicolor LED Light Included)
- 4. Soaking Option Only (Multicolor LED Light Not Included)



Jetting Options

Hydro Massage

- Hydro Massage Pump 5AMP 600W *
- · Hydro Massage Intensity Dial Control
- · Ozone Sterilization 1AMP
- 13 jets
- On/Off Push Control In-line Water Heater 5.5AMP 650W *

Air Massage

- Air Massage Pump 4.5AMP 486W *
- · 3 Speed Pump
- Auto-purge (Activates 20 minutes after pump shutdown)
- 16 jets
- · On/Off push control

Two-Piece Fast Fill Faucet

- Up 10 16 GPM @ 60 PSI an ideal in-home plumbing conditions
- Two 5' water supply lines with 3/4" connectors

Faucet Options

• Pull out, hand held, chrome plated hand shower with a 5' ft. retractable stainless steel braided hose



Microbubble Therapy

- Air Pressure Pump 10AMP 1200W *
- · Pressure Tank
- · On/Off push control

Electrical Requirements

Dedicated GFCI protected electrical line(s) required

Optional Features

- 1.Heated Seat and Backrest 4AMP 470W
- 2. Digital Controller

Note: Multicolor LED light .04AMP with On/Off push control is included with the following dual packages: Hydro + Air, Hydro + Micro, Hydro + Hydro


Disclaimer*: AMP value for each pump may change based on availability. Please verify before purchase. (800.480.6850)

Warranty

- Lifetime limited* warranty on shell, frame, door, and parts to original purchaser/Address
- Labor or installation is not covered please refer to the Ella warranty certificate
- Non Ella brand faucets covered under manufacturers original warranty




Front Entry Acrylic Outward Swing Door Walk-In Bathtub Specifications





Ella 2" T-type Dual Port Floor Drain

Dual Drain Technology - Two 2 Inch Independent Floor Drains





Supply Lines, Electrical Connection, & Drain Options

Two 3/4" connector water supply lines included with Ella Fast Fill Faucets



Connect to Shut Off Valves (not included)





All electrical fixtures connect to a dedicated GFCI protected outlet.



Use a drain cap to close unused drain port.



T-Type four (4) 2" drain ports allow for the drain pipe to be installed in either direction.

Images below show examples of PVC pipe connections (not included). Reducers can be used to connect smaller drain pipes.







Ella 2 Piece Single Lever Fast-Fill Faucet

Description

Solid brass spout chrome finish single lever high flow bathtub faucet with diverter button Two (2) 3/4" 5' braided stainless-steel supply lines Pull out hand shower mixer with 5 settings and 5' braided hose in a Chrome or Brushed Nickel finish.

Flow

- Hand shower is limited to 1.9 GPM (7.5L/min)
- Faucet fill rate designed for 18 GPM (68.1L/min)

Cartridge

- · 40mm high flow cartridge design
- · Nonmetallic/nonferrous and stainless-steel material

Standards


- Third party certified to meet: CSA B125.1, ASMEA112.18.1, ICC117.1 and all applicable requirements referenced therein
- · Certified to ANSI/NSF 61/9
- · ADA for lever/handle
- · IAPMO R&T UPC certified





NOTE: This faucet is designed to be installed through:

2-1/2" diameter hole for faucet, 1/3" diameter hole for mounting rods, and a 7/8" diagonal hole for the hand shower.





Replacing A Valve Cartridge

Step-by-step Instructions to replace a valve cartridge for Ella 2-piece faucets.

Step.1 Remove the Hot/Cold screw hole cover.



Step.2 Use an Allen wrench to remove the handle Screw.



Step.3 Take out the handle and remove the brass escutcheon



Step.4 Use a wrench to unscrew the pressure cap.



Step.5 Remove the cartridge and replace it with new piece.



