





PAD-CFSM

Custom Flex Suction Mount for 7-14 Inch Tablets INSTRUCTION MANUAL

Thank you for choosing CTA Digital's product. We hope that you will enjoy using it. Please follow the guidelines and instructions as laid out in this instruction manual.




Package Contents:



Instructions:

1. Attaching Foam Pad to Tablet Holder



Select the appropriate foam pad according to the thickness of your tablet (or tablet in its case), then press adhesive side into center of the tablet holder.

Use this table to determine the appropriate foam pad to use with your tablet.
Note: sizes refer to total tablet size with or without a case.

Foam Pad Thickness	Tablet Thickness:
1mm	0.67-1.06in / 17-27mm
5mm	0.51-0.91in / 13-23mm
10mm	0.31-0.71in / 8-18mm

2. Installing Custom Flex Suction Mount to the Windshield




Press the SUCTION BASE on the windshield and tighten the TURNTABLE.




Keep the ARM closed to the central console will reduce the vibration

3. Adjusting the Flex Arm




1. Twist the SCREW KNOB of the arms anticlockwise to release the connection.



2. Adjust the arms to your favorite position and then tighten the SCREW KNOB clockwise.

4. Installing your Device and Adjusting the Tablet holder

***Disclaimer - Ball Joint Warning**



1. Press quick release button on side of tablet holder to release the adjustable end. Insert tablet corner against the spring arm, then push adjustable arm down against opposite corner. Be sure it is as snug as possible.

2. Tablet holder rotates 360 degrees for custom viewing angles.

DO NOT attempt to adjust, tilt, or rotate any ball socket joints while it is fully tightened. Any such action will result in possible damage and loss of integrity of product functioning at full capacity. Manufacturer will not be responsible for any such actions by any person.



Caution

Please be sure to fasten all the screws were tightened securely while using the stand.
Not for use while driving.
Max loading : 1.5KGS(When Moving) 3.0KGS(When Immobility)

SUPPORT@CTADIGITAL.COM