I Specifications

| 1 Specifications | | | |
|------------------|-----------------------------|-----------------------------|-------------------------------|
| | | UL | CE |
| XLC-2000/3000* | | XLC-2000/3000 | XLC-2000/3000 |
| General | Power Supply | AC120V / 60Hz | 220V ~ 240V / 50Hz |
| | Power Consumption | 1270W | 1670W |
| | Power Cord Length | 4 ft. | 1.8m |
| | Water Pressure | 10.7 ~ 106.6 psi | 0.75 ~ 7.5kgf/cm ² |
| | Elongated Dimension (WxDxH) | 16.0x20.8x5.7 | 406X528X145 |
| | Round Dimension (WxDxH) | 16.0x19.5x5.7 | 406X496X14 |
| | Small Dimension (WxDxH) | 16.0x18.5x5.7 | 406X470X14 |
| | Weight | 10.1lb | 4.6kg |
| Wash | Power Consumption | 1200W | 1600W |
| | Wash Volume | 0.16gal / min. | 0.7 L / min. |
| | Bidet Volume | 0.16gal / min. | 0.7 L / min. |
| | Sitz Bath Volume | 0.16gal / min. | 0.7 <i>l</i> / min. |
| | Nozzle Position Control | 5 Steps | 5 Steps |
| | Water Pressure Control | 5 Steps | 5 Steps |
| | Water Temp. Control | 4 Steps | 4 Steps |
| | Safety Device | Temp. Sensor, Bimetal, Fuse | Temp. Sensor, Bimetal, Fuse |
| Dry | Power Consumption | 250W | 250W |
| | Dry Temp. Control | 5 Steps | 5 Steps |
| | Safety Device | Bimetal, Fuse | Bimetal, Fuse |
| Heated Seat | Power Consumption | 55W | 55W |
| | Seat Temp. Control | 4 Steps | 4 Steps |
| | Safety Device | Temp. Sensor, Fuse | Temp. Sensor, Fuse |
| | Seat Sensor | Body Sensor | Body Sensor |
| | | | |

^{*}Available in round or elongated seat sizes



Infinity Bidet™ 71 Ruths Place, Suite #8 Sequim, WA 98382 USA Tel : 1-800-681-0753 / Fax : 1-800-681-4029

Due to the differences in prints, the colors shown here can not be represented with all their true qualities



The Bathroom of the Future...Is Here Today







03 Points



Ceramic Instant Heating

The newest and most energy efficient way to heat water – continuously heats water for as long as you need



Cold-Warm / Sitz Bath

Exclusive feature to relieve many medical conditions



Child Wash

Specialized nozzle position, water pressure/ temperature for sensitive children and elderly people





Bubble Wash

Aerated water wash aids cleansing



Pulse

Pulse wash repeatedly cycles from weak to strong



Self-Cleaning

To wash and maintain clean nozzle that operates before and after every use



Adjustable Nozzle Position

Users can adjust nozzle position to desired setting



Compact Design

Fits most 1 and 2 piece toilets. Sleek-Low profile-Contoured design



Self-Diagnosis

Self-diagnosis function continuously monitors operation



Seat Sensor

User must be sitting to activate controls



Water Purifying Filter

Specialized ion water filter (optional)



Vertical Nozzles

Vertical nozzles provide improved hygiene use



Control Arm XLC-2000

Easy touch and simple waterproof switching



Remote Control XLC-3000

Easy touch and simple waterproof switching



Detachable Main Body

It is easy to install and detach for cleaning or moving

