



## **NEW INSTRUMENTS 2023**

## **Small-Incision Capsulorhexis Forceps with Cross-Action and Scale**

**CATARACT** 



### **Escaf Nucleus Manipulator**




### Amado Haptic Holder "Perfect Flanger"

Designed for attaining a standardized flange for intrascleral intraocular lens fixation.



Reference cylinder eliminates the need for rulers.




Grooved tip gently holds the haptics or sutures with no kinking.\*

4-211T




#### **IOL COMPLICATIONS MANAGEMENT**

#### **Holz Zonule Defender**



# Intraocular Lens Extraction Forceps for Cartridge Pull-Through Technique, 18 Ga

- Specially designed for Cartridge Pull-Through Technique
- Narrow and long tips grasp the IOL securely



\*Tip only. Handles are sold separately