

8-31/32"
(228)

OUTLINE OF CHASSIS
BASE PLATE (Item 11)

EcoSlender Mounting Template

TAPE THIS SHEET TO WALL FOR HOLES LOCATION



When printing the downloadable Hand Dryer Mounting Template, please ensure the PDF document is printed at Actual Size. If you are unable to print to scale, the use of the measurements on the installation template is paramount. Metlam Australia does not take responsibility for the incorrect print out of mounting templates which result in inaccurate mounting holes being drilled during Hand Dryer installation.

Important Information

This Product falls within the scope of the Waste Electrical & Electronic Equipment Directive 2002/96 EC. (WEEE)



6-1/16"
(154)

NOTE:

This Product should not be disposed of with household waste
Please recycle where facilities exist.
Check with your local authority for recycling advice.

Holes Location AFF for C-D Holes

General Purpose Suggested
51" (1295)

All Dim's
INCH (MM)

See OM for additional mounting heights suggestions for different age groups

B

A

5/32"
(4)


Ø 7/8" (Ø22)
ELEC.K.O

2-33/64"
(64)

5/32"
(4)

(Item 21)

Ø 7/8" (Ø22)
ELEC.K.O



1/4"
(6)



STRIP LENGTH
OR USE TIP TERMINALS
P/N A0242 (SEE OM)



1-27/32"
(47)

4-1/64"
(102)

SURFACE CONDUIT
ENTRY LOCATION

C

D