ORP/Temperature

ULTRAPEN™ DUIS BENEFITS: • Reliable Repeatable Results • Accurate

- Affordable
- · Easy to Use
- Rugged Design
- Ensure Product Quality
- Reduce Waste
- Protect the Environment

HIGH PERFORMANCE FEATURES

- Accuracy of ±10 mV ORP
- 3 Calibration Options with Automatic Solution Recognition
- Automatic Temperature Compensation in Calibration Mode
- 99.9% Pure Platinum Electrode
- Live or Hold Mode User Selectable
- Auto-Off Feature User Adjustable
- Proprietary Sensor Design
- Easy to Use One Button Control
- Rugged Design with Aircraft Aluminum Body
- Durable, Epoxy Encapsulated Electronics
- Waterproof
- Powered by One N Type Battery (Included)



ULTRAPEN™ PT1 Conductivity, TDS, Salinity & Temperature ULTRAPEN™ PT4 Free Chlorine Equivalent (FC5) & Temperature ULTRAPEN™ PT5 DO (Dissolved Oxygen) & Temperature ULTRAPEN™ PT6 Nitrate & Temperature ULTRAPEN™ PT7 Chloride & Temperature

PT3 COMES WITH:

- PT3 Pocket Tester Pen Battery Installed
- User Replaceable ORP Sensor Installed
- Protective/Hydration Cap
- Scoop
- Pocket Clip
- Holster
- Lanyard
- ORP Electrode Cleaning Paper
- Quick Start Guide





Water Quality Instrumentation Accuracy • Reliability • Simplicity

. . . Since 1957

PT3 MEASUREMENT MODES

MODE	METHOD OF MEASUREMENT
Hold (default)	Once stabilized, the readings are captured then displayed.
LIVE	Real-time readings are displayed continuously during measurement.

SPECIFICATIONS

ORP Range:	-1000 mV to +1000 mV
ORP Accuracy:	± 10 mV
ORP Resolution:	1 mV ORP
Temperature Range:	0 - 71°C / 32 - 160°F
Temperature Accuracy:	± 0.1°C
Temperature Resolution:	0.1°C / 0.1°F
Time to Reading Stabilization:	10 - 45 seconds
Power Consumption:	Active Mode: 30 - 140 mA, Sleep Mode: 2 µA
Temperature Compensation:	Automatic In Calibration Mode From 15°C to 30°C
Physical Dimensions:	17.15 cm L x 1.59 cm D or 6.75 in. L x 0.625 in. D
Weight:	50.4 g / 1.78 oz. (without soaker cap and lanyard)
Case Material:	Anodized Aircraft Aluminum with Protective Coating
Battery Type:	One N type, Alkaline, 1.5 V
Calibration Standard Solutions:	ORP80, ORP260, ORP470
Operating/Storage Temperature:	0 - 55°C / 32 - 131°F
Enclosure Ratings:	IP67 and NEMA6
CE	Electrostatic discharge to the PT3 may cause it to spontaneously turn on. If this occurs, the PT3 will turn off.
EN61236-1: 2006 – Annex A: 2008:	



WARNING! These products can expose you to chemicals including Di(2-ethylhexyl)phthalate (DEHP), which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

ACCESSORIES

STANDARD SOLUTIONS FOR CALIBRATION:



The ULTRAPEN™ PT3 requires Myron L® Company 80mV Quinhydrone, 260mV Quinhydrone, or 470mV MLC Light's ORP Standard Solutions for wet calibration and Sensor Storage Solution for proper storage.

Order Model Numbers:

ORP802OZ 80 mV, Kit, Quinhydrone/pH7 2 oz.
ORP2602OZ 260 mV, Kit, Quinhydrone/pH4 2 oz.
ORP4701OZ 470 mV, MLC Light's Solution 1 oz.
ORPCALKIT Calibration Kit, ORP, 80 mV, 260 mV, 470 mV
SS2OZ Storage Solution 2 oz.
(For additional information and calibration kits available, contact the Myron L® Company.)

ORP ELECTRODE CLEANING PAPER

Routinely cleaning the platinum electrode will keep the sensor free of build-up that can affect the speed and accuracy of ORP measurements. Instructions for use are included with the paper. Order Model Number:

OECP-25 QTY 25 OECP-100 QTY 100

REPLACEMENT ORP SENSOR

The ULTRAPEN $^{\text{TM}}$ PT3 features a user replaceable ORP sensor with a unique porous liquid-junction. Installation instructions included with sensor.

Order Model Number:

RPT3 Replacement ORP Sensor

MYRON L® WARRANTY

The PT3, excluding the sensor and battery, has a one (1) year limited warranty. The ORP sensor has a six (6) month limited warranty.

2450 Impala Drive Carlsbad, CA 92010-7226 USA Tel: +1-760-438-2021 Fax: +1-800-869-7668/+1-760-931-9189 www.myronl.com Built On Trust. Founded in 1957, the Myron L® Company is one of the world's leading manufacturers of water quality instruments. Because of our commitment to product improvement, changes in design and specifications are possible. You have our assurance any changes will be guided by our product philosophy: accuracy, reliability, and simplicity.



PT3DS r4-20a