# Arducam®



# **Datasheet**

8MP Autofocus USB Camera Module **B0447C** 

# **CONTENT**

- 1. Purpose
- 2. Effect
- 3. Technical parameters
- 4. Board Dimension Diagram
- 5. Imaging
- 6. Camera Parameters Interface
- 7. Function Inspection Criteria
- 8. Visual inspection criteria
- 9. Reliability Test
- 10. Packaging requirements
- 11. Other

Version	Compile	Auditing	Authorize	DATE
V1.0	Bin L	Kai Z	Lee J	04.18.2023

## 1. Purpose

In order to fully describe the technical specifications referred to in technical cooperation, it usually needs to be expressed by a complete set of documents. As part of this, this datasheet specifies the specific technical specifications that a camera module should meet and is binding on this model.

## 2. Efficacity

This datasheet shall prevail if this it's inconsistent with the specifications in the general technical specifications of such goods.

## 3. Technical Parameters

Image Sensor				
Resolution	8MP			
Chroma	Color			
Shutter Type	Rolling shutter			
Optical Format	1/3.2"			
Output Format	YUYV/MJPG			
Pixel Size	1.4um x 1.4um			
Sensor Active Area	3264(H)x2448(V)			
	MJPG:			
	30fps@3264×2448/2592×1944/1920×1080/1600×1200/1280×			
	720/640×480			
	YUY2:			
Frame rate	1fps@3264×2448 2fps@2592×1944			
	5fps@1920×1080/1600×1200			
	10fps@1280×720			
	30fps@640×480			
Lens				
Focus Type	Autofocus			
FOV	63°(H)			
Lens Mount	M8.5±0.25			
F.NO	2.0±5%			
EFL	3.543			
USB Interface				
Interface	USB 2.0 device			
Connector	B4B-ZR			
UVC Compliant	No additional drivers required			

Website: <a href="mailto:www.arducam.com">www.arducam.com</a> | Email: support@arducam.com


B0447C Datasheet Proprietary to


## Arducam

Electrical and Mechanical				
Operating Voltage	DC 5V +/- 5%			
Working Current	Max 300mA			
Operating Temp.	-4°F-158°F(-20°C to 70°C)			
Camera Board Size	38mm x 38mm*7.3mm(Hole Pitch: 34mmx34mm, 28mmx28mm)			
Functionality and Compatibility				
Audio	Single Microphone			
Supported OS	Windows, Linux, Android, and MAC			
Sample Application	AMCap-Windows Camera application for Video and Still Capture			
UVC Controls  Brightness, Contrast, Hue, Saturation, Sharpness, Gamma, V Balance, Backlight Comp, Gain				

# 4. Lens & Board Dimension Diagrams

Unit: mm






# 5. Imaging




## 6. Camera Parameters Interface


## - Video Proc Amp




#### - Camera Control



## - Video Capture Pin





## 7. Function Inspection Criteria

#### 7.1 Function definition:

Camera module electrical performance and image quality.

#### 7.2 Inspection methods

- Staff: Visual inspection personnel need to be trained and have normal color recognition ability. Their vision should be above 1.0 (or more than 1.0 after correction is acceptable), and their color discrimination ability can pass standard tests.
- Tool: Connect the computer, inspect images with AMCap software.
- Distance and Time

Observation distance: 30~55cm

Observation time for each surface: 3~5seconds

• Inspection condition: Visual inspection should be performed under unobtrusive fluorescent lamps, and its minimum illumination should be above 100 feet of candlelight, or 60W fluorescent lamps, inspected at 1.5m distance.

## 7.3 Accept criteria

- The image has no mess, color screen and discoloration.
- There is no white spot, black spot, dirt or dark angle in the image.
- The image is same clear on all corners

## 8. Visual Inspection Criteria

#### 8.1 The definition of the appearance

Camera module appearance.

#### 8.2 Test methods

• Staff: Visual inspection personnel need to be trained and have normal color recognition ability. Their vision should be above 1.0 (or more than 1.0 after correction is acceptable), and their color discrimination ability can pass standard tests.

Website: www.arducam.com | Email: support@arducam.com

B0447C Datasheet Proprietary to

#### Arducam

Distance and Time

Observation distance: 50~75cm,

Observation time for each surface: 3~5seconds

• Inspection condition: Visual inspection should be performed under unobtrusive fluorescent lamps, and its minimum illumination should be above 100 feet of candlelight, or 60W fluorescent lamps, inspected at 1.5m distance.

• Observation angle: Observation angle between  $40^{\circ} \sim 50^{\circ}$ .

#### 8.3 Accept criteria

• Cleanliness: Parts must be free of stains, dust, grease, and other stains. Smudges due to transportation materials are acceptable if they can be blown away or wiped off.

• Assembly surface: The parts to be assembled should avoid scratches, gouges, dents, bends, cracks, indentations, abrasions or other defects caused by improper assembly.

## 9. Reliability Test

Items	Condition	Specification	
High Temperature Test	Temp.: 80°C	No abnormal	
Ingh Temperature Test	Time: 96H		
Low Temperature Test	Temp: -20°C	No abnormal	
Low remperature rest	Time: 96H	No abnormai	
П	Temp: 60°C	No abnormal	
Humidity Test	Humidity: 80-85%		
	Time: 24H	No abnormal	
Cable Tensile Strength   Test	Loading weight: 4KG		
	Time: 60s		
	Hight: 60CM	Electric normal	
Drop Test	Number of times: 10		
	On the wood	1	
	Vibration machine vibration frequency to 50Hz	Electric normal	
Vibration Test	Vibration amplitude: 1.5MM;		
LICD Connector	Vibration time: 30 Minutes	E141	
USB Connector	Number of times: 250	Electric normal	

Website: www.arducam.com | Email: support@arducam.com

## 10. Packing Request

- Products should be strictly based on product characteristics to develop corresponding packaging standards and follow the implementation to ensure that the product is used within the specified use and storage period, to achieve anti-static, moisture-proof, shock-proof, mildew-proof, anti-barbaric handling and other signs and related warranty requirements. Product packaging should be marked: Supply-side name / logo, Product Model specifications, containing the number, production date / batch number and order number.
- The product's outer packaging should be marked with: supplier name / sign, product model specification, built-in quantity, production date / batch number and order number.
- The packing and packing scheme are based on the customer's requirements, and the two parties will negotiate the specific details. The sealed samples shall prevail.

#### 11. Others

- Changes to this acknowledgement need to be confirmed by both parties, and any modification by either party is invalid.
- This acknowledgment must be signed and returned within seven working days of receipt by the client, late regarded as the default.

Distribution Partner:



shop.scorpion.vision 🗘 +44 (0) 1590 679333 @ sales@scorpion.vision