



FRONT VIEW



BACK VIEW



CAPACITY
 Microwow One-Touch 1000..... 900ml
 Microwow One Touch 1500..... 1340ml

BEFORE FIRST USE

- Remove any labels with warm water and detergent.
- Rinse the casserole well and dry thoroughly.

INSTRUCTIONS FOR MICROWAVE USE

- The casserole is only meant for reheating pre-cooked food in the microwave oven, not cooking.
- Only reheat for a maximum of 5 minutes in the microwave oven.
- Ensure that the casserole is placed **without the lid** centrally on the glass turntable.
- The casserole is not suitable for use in the Grill, Convection or Combination mode in your microwave oven.
- Do not use aluminium foil to wrap any food inside of the casserole whilst re-heating in the microwave.
- Please maintain a gap of 15 minutes between two reheating cycles.

CLEANING

- The casserole is completely dishwasher safe or can be hand washed.
- Always ensure it is dried thoroughly after washing.
- If using a dishwasher, wash on a normal wash cycle. Avoid intense dish washing cycles to prolong the life of your casserole.
- Keep the casserole upside-down on the top rack of your dishwasher for better cleaning.
- It is recommended not to use lemon-scented detergents, as it may reduce the surfaces shine.

WARNINGS

- Due to the risk of burning, always handle with care.
- Never pour cold water (or any other cold liquids) into the casserole that is still hot.
- Please keep the hot casserole away from children at all times.
- The stainless steel inside the casserole becomes very hot after reheating. Therefore, always use suitable serving utensils to take the food out to avoid the risk of burning.
- Always use oven gloves when removing the casserole from the microwave.
- Only use the casseroles for their intended purpose. Follow all instructions carefully.



Voltage Business Centre, Units 1 - 3 | 6 Mollison Avenue, Enfield, EN3 7XQ
 T: 01992 716 070 | F: 01992 700 538 | E: info@sqprofessional.com

WWW.SQPROFESSIONAL.COM

SQIM 8345-8346-8347-8348-8349-8350 11-05-2021 V4 | SQ Professional Ltd © 2021 All rights reserved
 Image is for illustration purposes only. Actual product may vary.



INSTRUCTION MANUAL

MICROWOW ONE-TOUCH
 INSULATED MICROWAVEABLE CASSEROLE

1000 | 1500



**BEFORE USING THIS PRODUCT, PLEASE CAREFULLY
 READ THE FOLLOWING INSTRUCTIONS**

SQIM 8345-8346-8347-8348-8349-8350 11-05-2021 V4