**DEPENDAPLAST** technology | quality | construction



# The Dependaplast range has been updated to include plasters made from modern, premium materials, with superior qualities.

All ranges are packed into smart, compact, dispenser boxes, providing clear, easy access to contents with the main focus being an upgrade to modern fabrics and huge savings on storage.

## What's new?

DEPENDAPLAST

DEPENDAPLAS

DEPENDARIAS

• Fabric Plasters have been updated to a modern, hi-tech, slimmer material.

DEPENDAPLASI

DEPENDATE IS

- All plasters are latex-free.
- Boxes are redesigned to fit the plasters and are easier to select.
- Improved quality, same price.
- Vast savings on carriage and warehouse space.



Dependaplast plasters offer a full and comprehensive range

of the most popular shapes and sizes. Plasters are now neatly packed in a variety of boxes, allowing for clear, easy access, and because the boxes are smaller, save on storage too. Ideal for refilling first aid kits or to keep as backup supplies. All Dependaplast plasters are latex-free with a Rayon wound contact layer.

## What's the difference?

### **Multisoft Plasters**

The latest non-woven polyester fabrics are used in Multisoft to provide a soft, highly flexible dressing that is thinner, lighter and more conformable that regular fabric plasters. This product is ideal for activities that require high levels of dexterity, like sewing or PCB assembly. Multisoft uses high-tech acrylic adhesives to provide a really secure fixing, that is skin friendly and low allergy. Multisoft is tough, yet gentle, making it the correct solution for delicate skin, and perfect for children or the elderly.

## Advanced Fabric Plasters

**New Improved** Dependaplast Fabric Plasters, use modern hi-tech thinner extra flexible fabrics that are more comfortable, conformable and easy to wear. The elastic fabric stretches in all directions, ideal for covering joints and skin folds with ease and comfort. The fabric is coated in a hydrophilic polymer making it water repellent and washproof. The new super-sticky zinc oxide adhesive ensures that Dependaplast Fabric Plasters remain stuck firmly in place. The adhesive comes cleanly away, avoiding unsightly plaster marks being left on the skin.

## Traditional Heavyweight Plasters

Using traditional heavy elastic fabric, offers extra cushioning and physical protection of wound sites. Ideal for outdoor use or applications requiring a more robust physical barrier. Traditional Zinc Oxide adhesive ensures that the plaster will stay firmly in place in the most demanding environments.

### Washproof Plasters

Flexible PU plastic film is used to ensure a super-thin, flexible, washproof plaster. The membrane is moisture vapour permeable, allowing the skin to breathe, without the need for physical perforations, keeping the adhesive securely in place, whilst acting as a complete barrier to water, virus, bacteria and fungi. High-tech acrylic adhesive provides a really secure fixing, but is skin friendly and low allergy.

## Blue Plasters

Whilst incorporating all of the modern features of Dependaplast Washproof Plasters, the Dependaplast Blue Plaster range provides a bright blue colouration that makes them instantly visually detectable should it accidentally come into contact with food. An aluminium strip located behind the dressing pad is clearly detectable to metal detection devices in food processing facilities.

## Childrens Plasters

All the modern properties of our washproof plasters, but printed with a fun handprint design.

## What are they made from?

#### PROTECTIVE FILM

Easy to remove without touching the wound pad.

#### WOUND CONTACT LAYER

The dressing pad on all Dependaplast Plasters incorporates a wound contact layer that is made from Rayon, a man-made fibre that is so slippery, it prevents adhesion to a wound and enables painless removal.

#### ABSORBENT LINT

Modern high-absorbency materials.

#### FOIL (BLUE FOOD ONLY) Metal detectors will reject food contaminated by lost plasters.

#### ADHESIVE

Our fabric and traditional heavyweight plasters use zinc oxide adhesive, making them super-sticky. For more sensitive skins, multisoft, washproof and blue plasters feature acrylic, low allergy adhesive.

#### PLASTER MATERIAL

Five great materials for every need including, Heavyweight Fabric, Fabric, Multisoft, Washproof and Blue.

#### OUTER PROTECTIVE WRAPPER


Made from paper to allow for easy fumble-free opening while maintaining sterility.





## The Packaging.

- Smaller boxes that fit the content.
- Tabbed lids, for secure closing.
- Plasters are packed so they can easily be identified and selected.
- Plaster type easily recognised through distinctively coloured lids.





## The Range.

MULTISOFT	ADVANCED FABRIC	HEAVYWEIGHT FABRIC	WASHPROOF	BLUE	CHILD
Non-woven, super-thin.	Stretchable fabric weave.	Excellent strength.	Soft, flexible	Metal detectable.	Soft,
Soft and flexible.	Water-repellent.	Cushioning protection.	washproof material.	Soft, flexible washproof	wash
Ideal for delicate skin. Low allergy. Latex-free.	Super-sticky adhesive. Lightweight. Latex-free.	Super-sticky adhesive. Latex-free.	Allows skin to breathe. Low allergy adhesive.	material. Allows skin to breathe. Low allergy	Allow Low a
0	0		Latex-free.	adhesive. Latex-free.	Latex
	Antonio Antoni	A Cardination of the second se	With proof Ration	Anternational An	
Box: 125W x 95H x 30mmD	Box: 125W x 95H x 30mmD	Box: 125W x 95H x 40mmD	Box: 125W x 95H x 30mmD	Box: 125W x 95H x 30mmD	Box: 1
REF SIZE QTY   572 6cm x 2cm 100	REF SIZE QTY   512 6cm x 2cm 100	REF SIZE QTY   2202 6cm x 2cm 100	REF SIZE QTY   532 6cm x 2cm 100	REF SIZE QTY   449 6cm x 2cm 100	REF 5310
<b>523</b> 7cm x 2cm 100	<b>513</b> 7cm x 2cm 100	<b>2203</b> 7cm x 2cm 100	<b>533</b> 7cm x 2cm 100	<b>543</b> 7cm x 2cm 100	633
524 7.5cm x 2.5cm 100	<b>514</b> 7.5cm x 2.5cm 100	<b>2204</b> 7.5cm x 2.5cm 100	<b>534</b> 7.5cm x 2.5cm 100	544 7.5cm x 2.5cm 100	
525 7.5cm x 5cm 50   528 Fingertip 50	515 7.5cm x 5cm 50   518 Fingertip 50	2205 7.5cm x 5cm 50   2206 Fingertip 50	535 7.5cm x 5cm 50   538 Fingertip 50	545 7.5cm x 5cm 50   548 Fingertip 50	
<b>529</b> Anchor 50	<b>519</b> Anchor 50	<b>2207</b> Anchor 50	<b>539</b> Anchor 50	<b>549</b> Anchor 50	
<b>526</b> Assorted 100	<b>516</b> Assorted 100	<b>2210</b> Assorted 100	<b>536</b> Assorted 100	<b>546</b> Assorted 100	
				Ran Hann	
<b>Box: 100W x 56H x 50mmD</b> <b>521</b> 4cm x 4cm 100	Box: 100W x 56H x 50mmD   511 4cm x 4cm 100	Box: 100W x 56H x 50mmD   2201 4cm x 4cm 100	Box: 100W x 56H x 50mmD   531 4cm x 4cm 100	<b>Box: 100W x 56H x 50mmD</b> <b>541</b> 4cm x 4cm 100	
	Antipation of the second	Antipation and antipation antipation and antipation and antipation and antipation and antipation and antipation antipati	Contraction of the second	En Reini	
Box: 95W x 56H x 40mmD   570 4cm x 2cm 100	Box: 95W x 56H x 40mmD   509 4cm x 2cm 100	Box: 95W x 56H x 40mmD   2200 4cm x 2cm 100	Box: 95W x 56H x 40mmD   530 4cm x 2cm 100	Box: 95W x 56H x 40mmD   448 4cm x 2cm 100	
A Constant of the second of th	A Constant Line of the second se	A Construction of the second s	A Constant of the second secon	A Constant of the second secon	
Box: 65W x 142H x 25mmD   556 2cm x 12cm 50	Box: 65W x 142H x 25mmD   555 2cm x 12cm 50	Box: 65W x 142H x 25mmD   2212 2cm x 12cm 50	Box: 65W x 142H x 25mmD   557 2cm x 12cm 50	Box: 65W x 142H x 25mmD   558 2cm x 12cm 50	
	entrementer entre		A manual distance of the second secon	A construction of the second s	
Wallet: 80W x 112mmH	Wallet: 80W x 112mmH	Wallet: 80W x 112mmH	Wallet: 80W x 112mmH	Wallet: 80W x 112mmH	
578 Assorted 10   522 Assorted 20	510 Assorted 10   520 Assorted 20	2208 Assorted 10   2209 Assorted 20	554 Assorted 10   553 Assorted 20	542 Assorted 10   540 Assorted 20	
			• • • • • • • • • • • • • • • • • • •		
			Box: 75W x 75H x 30mmD		

550 Spot - Perforated 100 5311 Spot 100 ILDRENS

t, flexible shproof material. , ows skin to breathe. v allergy adhesive. ex-free.



125W x 95H x 30mmD SIZE QTY 10 7cm x 2cm 100 Assorted 100