# UNIVERSAL WIRELESS KEYPAD

### **INSTRUCTIONS**

### **Copy and Assign**

MUST have an existing working remote

- Press button A and hold, while pressing button B - 4 times. Device will beep each time and green light flashed once every 2 seconds.
- Immediately press and hold original remote button to be copied for up to 20 seconds, until green light flashes quickly, then press the number (1,2,3 or 4) you want to assign the button to. Unit will beep and green light will stay on for 2 seconds.
- 3. Light goes out, Done.

### Set the door open Passcode

- Press B and then the admin passcode (Default 999999). Will beep twice and red light stays on.
- Press the button (1,2,3 or 4) you want to assign the passcode for and then A. Will beep twice and red light stays on.
- Now enter the 6-digit passcode you want to use and press B. Red light will flash then stay on.
- 4. Repeat step 3. Will beep twice and red light will flash.
- 5. Light goes out, **Done**.

# When using Code to open door/gate

If Pincode is CORRECT, green light with be on for 3 seconds, door will trigger.

If Pincode is INCORRECT, long beep and red light for 3 seconds.





For best copying results, position original remote here

### **Change Admin Passcode**

- Press B and then the current admin passcode (Default 999999). Will beep twice and red light stays on.
- 2. Press 1 and then B. Will beep twice and red light stays on.
- 3. Now enter the 6-digit passcode you want to use and press B. Red light will flash then stay on.
- 4. Repeat step 3. Will beep twice and red light will flash.
- 5. Light goes out, Done.

## **Handy Hints**

When creating a passcode, it is a good practice for the first number to match either 1,2,3 or 4 that the passcode position applies to. Eg; passcode for button 3=377477

Whenever programming, if something is wrong with sequence, LED will flash and beep 10 times. Start process again.



# **COMPATIBILITY CHART**

In the event that this remote is capable of cloning any remotes not listed below, Remote King warns that any attempt to clone a remote which is protected by patent is illegal and Remote King strongly opposes such acts and considers it a direct infringement of the rights of the patent holder.

ACM	TX2, TX2 COLOR, TX4
ADYX	TE4433H BLUE, 433-HG BRAVO
AERF	COMPACT, HY-DOM, MERCURI B, MERCURI C, SABUTON, MARS, SATURN, ST3/N, TERRA, TMP-1, TMP-2, UNITECH
ALLMATIC	BROWN, BROWN RED, BRO.OVER, PASS, MINIPASS, TECH3
APERIO	GO, GO PRO, GO MINI
APERTO (Sommer)	TX02-434-2, TX02-868-2 BLUE, 4025 TX02-868-2, 4022 TX02-434-2, 4020-TX03-434, TX-03-868-4, 4013, TX03-434-4
APRIMATIC	TR2/TR4, TM4, TXM
ATA	PTX4 BLUE, PTX4 PINK
AVIDSEN	104251, 104250, 104250 OLD, 104250 RED, 104257, 104350, 654250
BALLAN	FM400, FM400E, FM404B, 4013
BENINCA	TO.GO.WV, TWV, ROLLKEY, APPLE, LOT WCV, CUPIDO, TO.GO.QV, IO, LOT2WCV, LOT1W, LOT2W LOT4W, LOT1WM, LOT2WM, T2W, T4W, APPLE
BESIDE	BEZAP, HIT
BFT	MITTO, MITTO M (MITTO2M/MITTO4M), MITTO RCB (MITTORCB02/RCB04), MITTO A (MITTO 2A/MITTO 4A), MITTO B, TRC(TRC2/TRC4). GHIBLI, MURALE, KLEIO, TE01, TE02, TE04, RB4 MURALE
CAME	T431,T434,TOP434A,TOP432,TAM432SA,TOP432NA
CARDIN	TRQ S449 (TRQ449100/ TRQ449200/TRQ449300/ TRQ449400), TRQ S449 GREEN (PRECODE), TXQ S449 (TXQ449200/TXQ449300/TXQ449400), TXQ S449 GREEN, TRQ S486 (TRQ486200/TXQ486400), TXQ S486 (TXQ486200/TXQ486400), S437TX, XRADO, S449, S476TX, S476TX2, S486
CASALI	JA33 AMIGO, GENIUS/CASALI A252RC
CASIT	ERTS92B, ERTS92T, ERTS476D, ERTS20DQ, ERTS476D, ERTS476Q
CASALI	JA33 AMIGO, GENIUS/CASALI A252RC
CELISA	S101, S102
CENTURION	CLASSIC,SMART
CHAMBERLAIN/ LIFT MASTER/ MOTOR LIFT	953ESTD, 371 LM, 971 LM, 84330E, 94334CE, 94333E/94334E/94335E, 9747E, 1A5639-7, 1A5477, 1A6487, 132B2372, 94330EML/9333EML/94335EML, 84330EML/84333EML/84335EML, 8747EML
PRASTEL	TC2E(4E), SLIM, BFOR, MPSTP2E, MPSTF4,

LIFT MASTER/ MOTOR LIFT	94333E/94334E/94335E, 9747E, 1A5639-7, 1A5477, 1A6487, 132B2372, 94330EML/9333EML/94335EML, 84330EML/84333EML/84335EML, 8747EML
PRASTEL	TC2E(4E), SLIM, BFOR, MPSTP2E, MPSTF4, MPSTF2RE, MPSTF4RE, MPSTP2E, MPSTP2E BLUE, MTE(MT4E, MT2E), TRQ-P(TRQ4P, TRQ2P), MPSTLE(MPSTL-1E, MPSTL-2E, MPSTL-4E)
PROEM	ER4C4ACS
PROGET	ETY_433N2, ETY_433N4
PROTECO	TX433, EUROMATIC
PUJOL	MARTE, P215, TWIN, VARIO MARS, VARIO OCEAN, NEO
QUASAR	433
RIB	LITHIO
ROPER	NEO, GO ROPER, GO MINI ROPER
SABUTOM	BROOVER, BROSTAR
SEA	SMART DIP
SEAV	BE HAPPY RS(BE-HAPPY-RS1, BE-HAPPY-RS2, BE-HAPPY-RS3), BE-SMART RSX, BE-HAPPY RH1, BE-HAPPY RH2, BE-HAPPY RH3
SECULUX	NEO
SILVELOX	Mhz 2007, QUARZ SAW
SICE	4790207
SIMINOR	CVXNL, MITTO, SIM433
SECURVERA	SV R2C, SV R4C, SV R6C
SERAI	OG/52, OG54, OG82, OG84, OG/28, OG48, OG62, OG64
SIMINOR	S433(2T-4T), ER2C4ACS, ER4C4ACS
SOMFY	TELIS, K-EASY, K-EASY NEW, K-EASY OLD, MITTO, KEY GO RTS, TELIS RTS, KEYTIS RTS, KEYTIS RTS NS, ALARMA
SOMMER	4010, 4011, 4014, TX03-434-2, 4013 TX03-434-4, 4020 TX03-868-4, 4026 TX03-868-2, 4022 TX02- 434-2, 4025 TX02-868-2, 4031 TX08-868-4
STAGNOLI	KALLISTO, VENUS AV223
TAU	250K-SLIMRP, 250K-SLIMR, 250T-4RP
TELCOMA	FM402, FM 402 E, FM400E, FM400
TOR LIFT	TORMIT4
VDS	TRQ P, ECO-R
VRAWFORD	EA433 4K, SMART2, SMART3
V2	PHOENIX 433-868, TXC, TSC, TRC, HANDY, SERIE ROYAL:TRR/43, TRR2/43, TRR4/43, PHOX 433

CLEMSA	MUTANCODE, T, T-8, E-CODE N, MASTERCODE MV
CPS	TCP3, CPS1, TCP3, CPS2, TCP3, CPS4, TCP3
DASPI DEA SYSTEM	HAPPY2, POPS 2, ZERO RC(ZERO 2RC, ZERO 4RC TR MIO, 133 1, 433 2, 433 4, GENIE, PUNTO S2, PUNTO 278, GOLDR, GENIE R 273, GENIE R-GT2N
DELMA	MIXARD 433 1, MIXARD 433 2, KING 433 2
DICKERT	MAHS433 01, MAHS433 04
DITEC	GOL, GOL4C, BIXLS2, BIXLP2, BIXAG4, BIXLG
DOITRAND	MPSTF2E, JAUNE
DOORMATIC	SAW
DOORHAN	TRANSMITTER 4
DUCATI	TSAW1, TSAW2, TSAW3, 124, TE2
ECOSTAR	RSE, RSC, RSZ
ELBE	501, 502, 504, 502A, 504A
ERREKA	IRIS, ROLLER 2, ROLLER 433, ROLLER 868, SOL433, SOL868, VEGA 433, VEGA 868
ELBE	501, 502, 504, 502A, 504A
ELCA	IRIS, ASTER 2, ASTER 1000, ASTER 1001
FAAC	XT4 433 RC, TM1 433 DS, TM2 433 DS, TM3 433 DS, 433L2, 433L4, TM22 433SLP, TM4 433 SLP, TML 433SLH, TML 868 SLH, DL 868 SLH, XT 868SLH, XT 433 SLH, T 868 SLH, T 433 SLH, XT 433 RC, TE433HG
FADINI	JUBI-SMALL, 433 M2, ASTRO 433-2, ASTRO 433-4, JUBI2/JUBI4
FERPORT	TAC1, TAC2, TAC4, TAC 1K, TAC 2K, TAC 4K, TAC2KR
GIBIDI	OPEN TMB, OPEN OUT, AU1600, AU1600 WOOD, AU1680, AU1680 WOOD, DOMINO
GULLIVER	MDW
GENIUS	AMIGO, AMIGOLD, KILO, BRAVO, ECHO
GENIE	GITR-3, GIT, GICT390, GIFT390-1, G3T-BX, G1T-BX, GM3T, GICTD, GIFTD
GIBIDI	AUO1590, AU1600, DOMI-NO AU 1680 WOOD, GIBIDI AU1610, AU1810, AUO3000, DTC 4334
HORMANN	HSM2, HSM4
JCM	NEO, TWIN, GO, GO PORTIS, GO NORTON
JAY	UBEI X1SL1,UBET11,UBET21,UBET31,UBET41,UBET61
KBLUE	ETH-TEL01

NOVOTRON 50, MNHS  NOLOGO ECO DIP  NORMSTAHL T433		
KLING   KUA, KUA E, KUA S	KEY	900TXB-42R, SUB44, TXB-44R, TXG-44R
LABEL         SPYCO, RJW4E           LEB         TMW           LINCE         LR2035           LIFE         FIDO           LINEAR         MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B           MHOUSE         TX4           MA         TX1, TX2, TX3           MARATEC         D101, D12, DIGITAL302, DIGITAL304           MERLIN/PROLIFT         M230T(PROLIFT), M430R(PROLIFT)           PROLIFT         M842(GREENREMOTE), M832(GREEN REMOTE), PROLIFT           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOTERNIA         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MICRO-NOVOTRON 504, MICRO-NOVOTRON 507, MICR	KING GATES	STYLO, CLIPPER
LEB         TMW           LINCE         LR2035           LIFE         FIDO           LINEAR         MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B           MHOUSE         TX4           MA         TX1, TX2, TX3           MARATEC         D101, D12, DIGITAL302, DIGITAL304           MERLIN/PROLIFT         M230T(PROLIFT), M430R(PROLIFT)           MERLIN/PROLIFT         M842(GREENREMOTE), M832(GREEN REMOTE), PROLIFT           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504,	KLING	KUA, KUA E, KUA S
LINCE LR2035  LIFE FIDO  LINEAR MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B  MHOUSE TX4  MA TX1, TX2, TX3  MARATEC D101, D12, DIGITAL302, DIGITAL304  MERLIN/ M230T(PROLIFT), M430R(PROLIFT)  MERLIN/ M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943  MHOUSE TX4, TX3, GTX4  MOOVO MT4G  MONSEIGNEUR ARC  NICE SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)  NORTON NEO, TXCD, GO NORTON, GO MINI NORTON  NOVOTECNICA BIXL2  NOVOFERM NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 31, MINI-NOVOTRON 50, MNHS  NOLOGO ECO DIP  NORMSTAHL T433  O & O T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R8-4, T.COM R8-2/T.COM R8-4  OG OG62, OG64  OPENOUT TMQ  PECCININ TX MENBRANA	LABEL	SPYCO, RJW4E
LIFE FIDO  LINEAR MCT-11, ACT-21, ACT-22, STING RAY ACT-31, STING RAY ACT-34B  MHOUSE TX4  MA TX1, TX2, TX3  MARATEC D101, D12, DIGITAL302, DIGITAL304  MERLIN/ PROLIFT M230T(PROLIFT), M430R(PROLIFT)  PROLIFT M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943  MHOUSE TX4, TX3, GTX4  MOOVO MT4G  MONSEIGNEUR ARC  NICE SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)  NORTON NEO, TXCD, GO NORTON, GO MINI NORTON  NOVOTECNICA BIXL2  NOVOFERM NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MICRO-NOVOTRON 30, MINI-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MICRO-NOVOTRON 30, MINI-NOVOTRON 504, MICRO-NOVOTRON 31, MICRO-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 504, MICRO-NOVOTRON 504, M	LEB	TMW
LINEAR	LINCE	LR2035
## STING RAY ACT-34B  MHOUSE TX4  MA TX1, TX2, TX3  MARATEC D101, D12, DIGITAL302, DIGITAL304  MERLIN/ PROLIFT ## M230T(PROLIFT), M430R(PROLIFT)  MERLIN/ PROLIFT ## M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943  MHOUSE TX4, TX3, GTX4  MOOVO MT4G  MONSEIGNEUR ARC  NICE ## SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)  NORTON NEO, TXCD, GO NORTON, GO MINI NORTON  NOVOTECNICA ## MININOVITRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 30, MININOVOTRON 506, MICRO-NOVOTRON 507, MICRO-NOVOTRON 30, MININOVOTRON 507, MININOVOTRON 508, MICRO-NOVOTRON 508, MICRO-NOVOTRON 509, MICRO-NOVOTRON 509, MICRO-NOVOTRON 509, MININOVOTRON 509, MICRO-NOVOTRON 509, MININOVOTRON 509, M	LIFE	FIDO
MA         TX1, TX2, TX3           MARATEC         D101, D12, DIGITAL302, DIGITAL304           MERLIN/ PROLIF T         M230T(PROLIFT), M430R(PROLIFT)           MERLIN/ PROLIFT         M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 50, MNHS           NOLOGO         ECO DIP           NORMSTAHL         T433           O & O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R4-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	LINEAR	
MARATEC         D101, D12, DIGITAL302, DIGITAL304           MERLIN/ PROLIF T         M230T(PROLIFT), M430R(PROLIFT)           MERLIN/ PROLIFT         M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 50, MNHS           NOLOGO         ECO DIP           NORMSTAHL         T433           O & O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R4-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	MHOUSE	TX4
MERLIN/ PROLIF T         M230T(PROLIFT), M430R(PROLIFT)           MERLIN/ PROLIFT         M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 51, MINI-NOVOTRON 50, MIN	MA	TX1, TX2, TX3
PROLIF T         M842(GREENREMOTE), M832(GREEN REMOTE), M844(GREENREMOTE), C945, C940, C943           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS, MINI-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 501, MINI-NOVO	MARATEC	D101, D12, DIGITAL302, DIGITAL304
PROLIFT         M844(GREENREMOTE), C945, C940, C943           MHOUSE         TX4, TX3, GTX4           MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOTERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 50, MI		M230T(PROLIFT), M430R(PROLIFT)
MOOVO         MT4G           MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MNHS433(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MICRO-NOVOTRON 501, MINI-NOVOTRON 50, MNHS           NOLOGO         ECO DIP           NORMSTAHL         T433           O & O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R8-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA		
MONSEIGNEUR         ARC           NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS-3-2, MICRO-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 50,	MHOUSE	TX4, TX3, GTX4
NICE         SMILO, FLOR-S, VERY-VR, INTI, FLO2, FLO4, FLOR-S ERA, ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)           NORTON         NEO, TXCD, GO NORTON, GO MINI NORTON           NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MICRO-NOVOTRON 50, MINI-NOVOTRON 50,	MOOVO	MT4G
FLOR-S ERA , ONE(ON), ON ERA, EGRO, PLANO, ONE(ON FM)   NORTON   NEO, TXCD, GO NORTON, GO MINI NORTON     NOVOTECNICA   BIXL2     NOVOFERM   NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 501, MINI-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 50, MNHS     NOLOGO   ECO DIP     NORMSTAHL   T433     O & O	MONSEIGNEUR	ARC
NOVOTECNICA         BIXL2           NOVOFERM         NOVOTRON 502-504-512MIX43-2, MTR40-2, MCHS43-2, MHS43(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON 30, MINI-NOVOTRON 504, MINCO-NOVOTRON 30, MINI-NOVOTRON 50, MNHS           NOLOGO         ECO DIP           NORMSTAHL         T433           O& O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	NICE	FLOR-S ERA , ONE(ON), ON ERA, EGRO, PLANO,
NOVOFERM	NORTON	NEO, TXCD, GO NORTON, GO MINI NORTON
MCHS43-2, MHS43(2-4), MNHS433(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON31, MICRO-NOVOTRON31, MICRO-NOVOTRON 50, MINI-NOVOTRON 50, MNHS           NOLOGO         ECO DIP           NORMSTAHL         T433           O & O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4-2/T.COM R8-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	NOVOTECNICA	BIXL2
NORMSTAHL         T433           0 & 0         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4 2/T.COM R8-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	NOVOFERM	MCHS43-2, MHS43(2-4), MNHS433(2-4), MCHS, MINI-NOVOTRON 504, MICRO-NOVOTRON 502, MICRO-NOVOTRON 504, MICRO-NOVOTRON31, MICRO-NOVOTRON51, MINI-NOVOTRON 30, MINI-
O & O         T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4 2/T.COM R4-4, T.COM R8-2/T.COM R8-4           OG         OG62, OG64           OPENOUT         TMQ           PECCININ         TX MENBRANA	NOLOGO	ECO DIP
2/T.COM R4-4, T.COM R8-2/T.COM R8-4  OG	NORMSTAHL	T433
OPENOUT TMQ PECCININ TX MENBRANA	0 & 0	T.COM, TWIN, TX.TWIN, TX2/TX4(NEO), T.COM R4- 2/T.COM R4-4, T.COM R8-2/T.COM R8-4
PECCININ TX MENBRANA	OG	OG62, OG64
	OPENOUT	TMQ
PORTAMATIC MPH01, MPH02	PECCININ	TX MENBRANA
	PORTAMATIC	MPH01, MPH02